


|           |                                    |          |                                              |
|-----------|------------------------------------|----------|----------------------------------------------|
| PART NAME | SERIES 60 DOORS (PLAIN & LOUVERED) | PART No. | 60-2340 THRU 60-2346<br>60-2540 THRU 60-2546 |
|-----------|------------------------------------|----------|----------------------------------------------|

**MATERIAL:**

DOOR \_\_\_\_\_ 20 GA. STEEL  
 VERTICAL SUPPORT \_\_\_\_\_ 18 GA. STEEL

**FINISH**

GRAY TEXTURED OR  
 ROYAL BLUE TEXTURED



DOORS MAY BE USED FRONT AND/OR REAR FOR SERIES 60 UNITS,  
 REAR DOOR ONLY FOR SERIES 2000 UNITS,  
 ALL INCLINED UNITS USE 42.438 HIGH DOOR FOR REAR.  
 DOORS CAN BE HINGED LEFT ONLY.

- - INDICATES DOOR SUPPLIED WITHOUT A VERTICAL SUPPORT.
- ☒ - (2) SETS OF (6) SLOTTED LOUVERS CENTERED ON DOOR.
- ☐ - (4) SETS OF (6) SLOTTED LOUVERS ON DOOR.
- △ - (4) SETS OF (12) SLOTTED LOUVERS ON DOOR.

| PART NUMBER |             | HEIGHT<br>H | A      | HEIGHT OF LOUVERS<br>B | FITS UNITS WITH<br>THIS PANEL SPACE |
|-------------|-------------|-------------|--------|------------------------|-------------------------------------|
| PLAIN       | LOUVERED    |             |        |                        |                                     |
| 60-2340 •   | 60-2540 • ☒ | 21.438      | 10.719 | 5.500                  | 21.000                              |
| 60-2341     | 60-2541 ☐   | 31.938      | 15.969 | 5.500                  | 31.500                              |
| 60-2342     | 60-2542 △   | 42.438      | 21.219 | 11.500                 | 42.000                              |
| 60-2343     | 60-2543 △   | 52.938      | 26.469 | 11.500                 | 52.500                              |
| 60-2344     | 60-2544 △   | 61.688      | 30.844 | 11.500                 | 61.250                              |
| 60-2345     | 60-2545 △   | 70.438      | 35.219 | 11.500                 | 70.000                              |
| 60-2346     | 60-2546 △   | 79.188      | 39.594 | 11.500                 | 78.750                              |