

# MODEL TL-2155



International size reference: 2/3AA, ER14335

## TECHNICAL DATA

(Typical values @+25°C for batteries stored for one year or less)



|                                          |                  |
|------------------------------------------|------------------|
| ■ Nominal capacity @ 0.5 mA, to 2V       | 1.45 Ah          |
| ■ Rated voltage                          | 3.6 V            |
| ■ Maximum recommended continuous current | 75 mA            |
| ■ Maximum pulse current capability       | 150 mA           |
| ■ Weight                                 | 12.4g (0.437 oz) |
| ■ Volume                                 | 5.7 cc           |
| ■ Operating temperature range            | -55°C to +85°C   |
| ■ U.L. Component Recognition, MH 12193   |                  |

***TADIRAN  
LITHIUM  
BATTERIES***



### AVAILABLE TERMINATIONS

|                            |               |
|----------------------------|---------------|
| SUFFIX- /S STANDARD        | 15-5155-21500 |
| SUFFIX- /T SOLDER TABS     | 15-5155-31500 |
| SUFFIX- /P AXIAL PINS      | 15-5155-41500 |
| SUFFIX- /PT2 RADIAL PINS   | 15-5155-36500 |
| SUFFIX- /TP POLARIZED TABS | 15-5155-52500 |
| SUFFIX- /PT POLARIZED TABS | 15-5155-53500 |



***LITHIUM XTRA***

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

Rev. B 04/03