




# Bullet Connectors


159-1612, 159-1615

**KOBI** CONN

Bullet Connects



159-1615



159-1612

Dimensions: In.

SPECIFICATIONS	
Type:	Solderless
Wire range:	16-14 AWG
Current rating:	15A max.
Voltage rating:	300V max. @ 75°C
Terminal material:	brass .016" thick
Insulation material:	vinyl
Insulation color:	blue
Temperature rating:	75°C

Date Last Revised: 6-27-05

Available from Mouser Electronics  
1-800-346-6873  
[www.mouser.com](http://www.mouser.com)

KC-300731

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

159-1612, 159-1615

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

159-1615 159-1612