


Caliper

- With depth gauge.
- Caliper and slide made of hardened, corrosion-free steel.
- Measuring surface and nonius satin chrome finished.
- Raised sliding surfaces.


Series 530

with upper locking screw




530-104

Measuring range mm	No.	Jaw length mm	Nonius		L mm	a mm	b mm	c mm	d mm	Mass g
			top	bottom						
0-150	530-104	40	1/128"	0,05 mm	231	40	21,0	16,5	16	143
0-200	530-114	50	1/128"	0,05 mm	288	50	24,5	20,0	16	180
0-300	530-115	64	1/128"	0,05 mm	403	64	27,5	22,0	20	355
0-150	530-312	40	1/1000"	0,02 mm	231	40	21,0	16,5	16	143
0-200	530-118	50	1/1000"	0,02 mm	288	50	24,5	20,0	16	180
0-300	530-119	64	1/1000"	0,02 mm	403	64	27,5	22,0	20	355
0-150	530-102	40	-	0,05 mm	231	40	21,0	16,5	16	144




Easy reading due to nonius scale inclined by 14 degrees




Series 530

with lower locking screw




530-316

Measuring range mm	No.	Jaw length mm	Nonius		L mm	a mm	b mm	c mm	d mm	Mass g
			top	bottom						
0-150	530-316	40	1/128"	0,05 mm	231	40	21	16,5	16	145
0-150	530-319	40	-	0,05 mm	231	40	21	16,5	16	145



Easy reading due to nonius scale inclined by 14 degrees



Functions

Depth gauge

Series 530

Specifications


Accuracy: DIN 862

Delivered in soft case

Optional accessories

Extension for depth measurement see page 148

530-102
with round depth gauge Ø 1,9 mm



Specifications

Accuracy: DIN 862

Delivered in soft case

Optional accessories

Extension for depth measurement see page 148

Metr. ISO-Gew				
Nenn- maß ext. Ø mm	Stig. Paso: Paso mm	Keil- fond inkl. truedo Ø mm	Bohr- maß inkl. Ø mm	Bohr- maß Ø mm
3	3/8	2,35	2,5	2,5
4	1/2	2,94	3,1	3,1
5	5/8	4,15	4,2	4,2
6	3/4	4,82	5	5
8	1	6,05	6,8	6,8
10	1 1/8	8,30	8,5	8,5
12	1 1/4	10,11	10,2	10,2
16	1 3/8	13,94	14	14
20	1 7/8	17,29	17,5	17,5
Whitworth				
Ø in	Grain	Ø mm	Ø mm	
1/4	20	4,72	5,0	
3/16	18	5,12	5,4	
1/8	18	5,48	5,7	
1/2	12	9,53	10,25	
5/8	11	12,52	13,25	
3/4	10	15,3	16,25	
7/8	9	18,61	19	
1	8	21,54	21,75	
		101995		

With Thread table
No. 101995 D
on the back side,
530-316 only