



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove)

Search Tips

Text Search: 'F512D6-6M18Y'

Your search criteria matched only one product, shown below

F512D6-6M18Y



- Pass all TIA/EIA-568-B.3 performance requirements
 - FOCIS-5 compliant
 - Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
 - Factory terminated and 100% tested for insertion loss
 - Insertion loss data recorded for every multimode cable assembly
 - Lifetime traceability of test data to a Q.C. number on each cable assembly
- * MTP is a registered trademark of US Conec Ltd.

▪ Part Number	F512D6-6M18Y
▪ RoHS Compliancy Status	Compliant
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS
▪ Part Description	Male MTP* to male MTP* plenum rated 12-fiber interconnect cable assembly (one male MTP* connector on each end on ribbon interconnect cable) – 50/125µm. Outside diameter: 5mm x 2.5mm.
▪ Product Type	MTP* Interconnect Cable Assemblies
▪ Length (m)	18
▪ Fiber Compatibility	50/125µm
▪ Fiber Cable Size	5mm x 2.5mm
▪ Fiber Type	Multimode
▪ Connector 1 Type	Male MTP*
▪ Connector 2 Type	Male MTP*
▪ Fiber Count	12
▪ Flammability Rating	Plenum (OFNP)
▪ Pricing Description	Male MTP*- Male MTP* Ribbon Interconnect Cable Assembly OM2 50µm, OFNP, 18m
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.