

5

4

3

2

1

26,06

1,27 ±0,13

AWG 28/7


colour coded

1,02


19 x 1,27 = 24,13 ±0,38

1,07

Wire ————— Cu tinned
Gauge ————— AWG 28/7
Voltage rating ————— 300 Vr.m.s
Conductor resistance ————— 221 mΩ/m
Capacity unbalanced ————— 49 pF/m
Impedance unbalanced ————— 105 Ω
Signal delay ————— 5,2 ns/m
Insulation material ————— PVC
Temperature rating ————— -20°C to +105°C
Flammability rating ————— UL: VW1
Insulation resistance ————— 1000 MΩ/km



Colour code sequence (in 10 steps):
brown, red, orange, yellow, green,
blue, violet, grey, white, black

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	SEK 18 Flat cable 20 poles, twisted pair, length per reel: 30,48 m colour coded, UL 20130, IEC 918	Maßstab/ Scale 10:1
			Detail.	25/10/05	JMDR			
			Insp.					
			Stand.					
33990	15/05/07	PK	HARTING EURL F-95972 Paris				TB 09 18 020 7006	Blatt/ Page 1 / 1
33247	25/10/05	JMDR						
Mod.	Dot.	Name				Sub.		