

OBSOLETE- USE PT-2735FPQ

Spec

Resonant Frequency (Hz)	3500 $\pm$ 500
Operating Voltage Max (Vdc)	3 ~ 28
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	10 at Rated Voltage
Sound Pressure Level Min. (dB)	88 at 30cm at Rated Voltage
Operating Temperature (°C)	-20 ~ +90
Storage Temperature (°C)	-30 ~ +100
Housing	ABS 777D UL94HB plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	4.1
Options	For other options contact factory

Dimensions: (units: mm)

