



Mallory Sonalert Products, Inc.

Part #:

SC616CPNR

Sales Outline Drawing

Revision:

C


Specifications:

| | |
|-----------------------|--|
| Sound Level Category | Loud |
| Mode of Operation | Chime @ 60% Duty Cycle |
| Voltage Rating | 6 to 16 VDC |
| Frequency | 2900 \pm 500 Hz |
| Loudness @ 2 FT | 82 to 92 Typ. |
| Current Draw | 6-23 mA |
| Housing Material | 6/6 Nylon, Color: Black |
| Storage Temperature | -40° to +85° C |
| Operating Temperature | -30° to +65° C |
| Panel Mounting | Recommended hole size is 1.25" (31.75mm). Thread front will fit standard 30mm (1.181") hole. |
| Knurled Nut | Used to attach part to panel. The max recommended torque is 10 in-lbs. |
| Weight (Typical) | 2.1 oz (60g) |
| NEMA 3R,4X, & 12 | Approved with use of ACC03. |
| Options | Please contact factory. |

Dimensions: Inches (mm)

cUL Recognized

ROHS Compliant



NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25" HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.