



Wire Connectors & Termination T&B Catalog Number:

10-417

78378610417

Status:

Active

Description:

Multi-Carton packed high temperature porcelain wire connector, HI-7.

Features

Three sizes accommodate #18-14AWG stranded
Copper
300 Volt rated.

Application

For high temperature applications over 105 degree C

General

Wire Range	#18-14
Minimum	2 #18
Maximum	4 #16

Dimension Information

Dimension A (inches)	27/32
Dimension B (inches)	17/32
Dimension C (inches)	7/32
Dimension D (inches)	13/32

Packaging

T&B Order Multiple	1000
Package in Units	1000
T&B Sold in UOM	Each
T&B Weight Per UOM	6.88 lbs. per 1000

Application Support

Product Overview Available on Website

Notes

Wire range size applies to stranded only.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E 9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com