

Round rigid conduits, oval conduits, flexible conduits and channelling.




ROUND RIGID CONDUIT

- Lengths 3m

- Colour Options

WHITE	BLACK
W	B

Please suffix product code with colour choice

 **BS 4607, BS 6099**

Note: Please see details relating to Thermal Expansion on page 92.

TYPE RNG Heavy Gauge

Super High Impact

Size	Ref	Packed	White	Black
20mm	RNG 20	90m		
25mm	RNG 25	90m		
32mm	RNG 32	30m		

Please note other sizes are available to special order.
Please contact us for further details.

TYPE RLG Light Gauge

Super High Impact

COLOUR White

Size	Ref	Packed
20mm	RLG 20W	90m
25mm	RLG 25W	90m

Prices for larger sizes on application.

For Export markets medium gauge conduit is available – details on request. Please order Conduit in Metres – NOT LENGTHS. SEE PAGE 68 FOR BENDING SPRINGS AND OTHER INSTALLATION EQUIPMENT.

OVAL CONDUIT

- Lengths 3m

Alternative lengths are available to order.

COLOUR White

 **BS 4607**

TYPE OVL

Super High Impact

Size	Ref	Packed
12mm	OVL 12W	150m
16mm	OVL 16W	150m
20mm	OVL 20W	150m
25mm	OVL 25W	150m
32mm	OVL 32W	75m
38mm	OVL 38W	75m

CHANNELLING

- Lengths 2m

Alternative lengths are available to order.

COLOUR White

TYPE CHN Standard Gauge

Super High Impact

Size	Ref	Packed
12mm	CHN 12W	150m
25mm	CHN 25W	150m
38mm	CHN 38W	100m