



Caster installed with jacking foot

Caster Kits

Access Caster Kits are designed to add limited mobility and leveling adjustment to your cabinet. Caster Kits are used with 'A' & 'B' type frames. Properly installed, the Caster Kit has a load capacity of 1400 Lbs. (635kg).

Part Number	Description	Shipping Weight	
		lbs.	(kg)
ACK	Caster Kit	6.2	2.8


Each Caster Kit includes four (4) locking casters and hardware.



Universal corner bracket with jacking foot standard with frame type 'A' & 'B'



Installed caster



Caster with jacking foot assembly for base skirt

Base Skirt Kit

The Base Skirt Kit is designed for use with Access cabinets installed on solid floors where bottom cable entry is required. Kits are also used to conceal casters and jacking feet. This kit includes four (4) each skirt brackets, extension nuts, metal panels and required assembly hardware. Attaches to the universal corner bracket that comes standard with frame type 'A' & 'B'.

Note: Caster Kit must be ordered separately.



Base skirt

Part Number See Color Code Below to Complete	Cabinet Width		Cabinet Depth		Shipping Weight	
Part Number	in.	(mm)	in.	(mm)	lbs.	(kg)
AMP66 —	23 ⁵ / ₈	600	26 ⁹ / ₁₆	675	10.2	4.8
AMP69 —	23 ⁵ / ₈	600	36 ¹ / ₃₂	915	17.1	7.8
AMP61 —	23 ⁵ / ₈	600	39 ³ / ₈	1000	17.6	8.0
AMP62 —	23 ⁵ / ₈	600	47 ¹ / ₄	1200	19.3	8.8
AMP86 —	31 ¹ / ₂	800	26 ⁹ / ₁₆	675	11.0	5.0
AMP89 —	31 ¹ / ₂	800	36 ¹ / ₃₂	915	17.9	8.2
AMP81 —	31 ¹ / ₂	800	39 ³ / ₈	1000	18.4	8.4
AMP82 —	31 ¹ / ₂	800	47 ¹ / ₄	1200	20.1	9.2

Color Code

A = Light Gray
B = Black