





VOLEX
GROUP
Standard Cord Details: 17000A 10 B1




Specifications

Certifications	  
Part Number	17000A 10 B1
Connector Type	C13
Plug Type	5-15P
Category	Plastic
Application	Detachable
Plug Catalog No.	US15S3
Connector Catalog No.	386A
Cable	SVT AWG 18x3
Jacket Color	Black
Length in Feet	3
Length in Meters	.91
Temperature Rating	60C
Packaging Units Per Carton	50
Color Coding	North America
Nominal OD in Inches	0.246
Nominal OD in Millimeters	6.25
Notes	See similar item 17002A for 18" length.



VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.

PACKAGING: FOLD & TIE



NOTES:

- 1) CORDAGE: 18/3 SVT, 60°C, BLACK
- 2) APPROVALS:
- 3) RATING: 10 AMP/125 VOLTS
- 4) FLAME RATING : FT2
- 5) PACKAGING: 50 PIECES/CARTON
- 6) ALL DIMENSIONS IN MILLIMETERS.

3	REVISED TO SHOW CHINA MANUFACTURED CORD	11/26/07
2	FORMAT UPDATE	08/20/04
1	C.U.D - NEW RELEASE	06/09/04
REV	DESCRIPTION	DATE



FORM IN71-07 REV.A

- ☒ Indianapolis, IN
- ☐ Conover, N.C.
- ☐ Freemont, CA
- ☐ Aguascalientes, MX
- ☐ Tijuana, Mexico
- ☐ Hermosillo, MX
- ☐ Clinton, AR
- ☐ Kanata, Canada

Proprietary Notice:

This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.

MATERIAL:

PLUG: PVC, BLACK
JACKET: PVC, BLACK

FINISH:

JACKET: SMOOTH

SCALE:
NOT TO
SCALE

ECD:
N/A

ITEM DESCRIPTION
CORDSET - NORTH AMERICAN
DETACHABLE POWER SUPPLY CORD (3')

TOLERANCE
UNLESS OTHERWISE
SPECIFIED
.XXX ± .005
.XX ± .02
.X ± .03
FRACT. ± 1/32
ANGULAR ± 1/2°

APPROVED

STC

DRAWN BY

ARK

DATE:

06/09/04

PART NO.

17000A 10 B1