

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	REV PER ECR 07-014387	19JUN07	JR	TM
	F	REVISED PER ECO-17-001534	08MAY2017	RS	DR

1 STAMP AMP 18-16, APPROX AS SHOWN.


2 WIRE INSULATION DIA IS
 $\phi 1.4-2.8\text{mm}$ [$\phi.055-.110$].

3 TONGUE MATERIAL THICKNESS IS 0.79 ± 0.05
[.031 $\pm$.002].

 APPLIES FROM EDGE OF WIRE BARREL TO CENTER OF STUD HOLE.

5 MATERIAL: BODY — COPPER PER ASTM B-152
SLEEVE — NYLON.

6 FINISH: BODY - TIN PLATE PER ASTM B-545
SLEEVE - COLOR, ORANGE.



1000	LOOSE PIECE	152884
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	19JUN2007
JR RUTH	

CHK	19JUN07
T MICHELUTTI	

APVD	19JUN07
------	---------

PRODUCT SPEC

APPLICATION 3550

APPLICATION SPEC

WEIGHT	
--------	--

CUSTOMER DRAWING



TE Connectivity

NAME	TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 18-16 AWG
------	--

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

SIZE	BASE CODE	MARKING NO	RESTRICTED TO
1		0	

A 300779(C=152884	—
-------------------	---

7/15/2017	00779	00000	
	SCALE	SHEET	REV

SCALE	5:1	SHEET	1 OF 1	REV	F
-------	-----	-------	--------	-----	---

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION

TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± 0.20 [.008]
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	.

[illegible]

5

6