

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PREEPORT, ILLINOIS

FED. MFR. CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING

JS-223

JS-223

M

DRAWING
NUMBER

X

X

ISSUE

3

REPLACES

RELEASE NO. SR-7354

CHECK

REVISIONS

A

COI6763

D W V

5 MAR 62

B

CO21422

W E G

20 JUNE 68

13 MAR '58

3 L S

CHECK

19 MAR '58

GCH

CHECK


11 MAR '58

J.E.C.


DRAWN

FO-50378

.09 WIDE X .031 THICK LEVER.



CORROSION RESISTANT STEEL ACTUATOR
AND BRACKET (TYPE 302).



DOTTED LINES INDICATE
BASIC SWITCH IN PLACE.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

WITH ISM
BASIC IN PLACE

OPERATING FORCE ----- 1 OZ. MAX.

RELEASE FORCE ----- 4 GRAMS MIN.

DIFFERENTIAL TRAVEL ----- .030 MAX.

OVERTRAVEL ----- .030 MIN.

ELECTRICAL DATA

CONTACT ARRANGEMENT

BREAK DISTANCE

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.018
THREE PLACE	(.000)	±.008
ANGLES		±

WEIGHT