



QCPC-6ARUVB-RD07F | 1696572

Quareo® Q2000 Series Managed Copper Patch Cord, Category 6A U/UTP, PVC, T568B, 7 ft, red

- Designed with integrated strain relievers, safeguarding circuit integrity
- Impedance matched for use in Quareo structured cabling systems
- Using Quareo Technology with connection point identification

Body Features

Cable Color	Red
Shield Style	U/UTP
Boot Type	Flexible strain relief
Cable Construction	PVC stranded
Conductor Material	Copper

Configuration Features

Wiring Pattern	T568B
Keyed	No

Dimensions

Length	2.13 m 7.00 ft
--------	------------------

Industry Standards

Flammability Rating	UL94-V0
Standards Compliance	ANSI/TIA/EIA-968-A CE IEC 60603-7 TICK N355

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Availability

Region	Australia/New Zealand EMEA Latin America North America
Comments	Standard colors: blue, gray and white (other colors are available upon request) Standard lengths: 4, 7, 10, 15, 25 and 50 feet (other lengths available upon request)

Product Type Features

Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6A
Product Type	Cable Assembly
System	Managed Connectivity

Usage Conditions

QCPC-6ARUVB-RD07F | 1696572

Operating Temperature -10 – 60 °C | 14 – 140 °F
Relative Humidity (Operating) 5%
Relative Humidity (Storage) 5%
Storage Temperature 0 – 50 °C | 32 – 122 °F

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant