





Coding style table	
	Style A: For connectors 6 poles
	Style B: For connectors 10 and 14 poles
	Style C: For connectors from 16 to 64 poles

Find further technical information on drawing DS 09181100001

	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.	
	All rights reserved Department EC PD - FR		Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2013-11-04	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp		Title SEK 18 male straight low profile				Doc-Key / ECM-Nr. 100541601/UGD/001/B 500000066836	
		Type TB	Number 09185XXX32X			Rev. B	Page 1/2

1		2		3		4				
A	Performance Level			Insulator Color	Contact Lenght ±0,3(mm)	Dimensions (mm)				
	PL3 : 50 mating Cycles No Gas Test	PL2 : 250 mating Cycles 4 days Gas Test	S4 : 0,76µm Au or equivalent PdNi			A Max	B	E		
	Nb of Contacts	Part Number	Part Number							
B	06	0918 506 7324	0918 506 6324	0918 506 5324	Grey	2,9mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7324	0918 510 6324	0918 510 5324			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7324	0918 514 6324	0918 514 5324			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7324	0918 516 6324	0918 516 5324			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7324	0918 520 6324	0918 520 5324			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7324	0918 526 6324	0918 526 5324			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7324	0918 530 6324	0918 530 5324			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7324	0918 534 6324	0918 534 5324			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7324	0918 540 6324	0918 540 5324			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7324	0918 550 6324	0918 550 5324			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7324	0918 560 6324	0918 560 5324			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7324	0918 564 6324	0918 564 5324			89,3	86,44	2,54 x 31 = 78,74	
C	06	0918 506 7324 001	0918 506 6324 001	0918 506 5324 001	Black	2,9mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7324 001	0918 510 6324 001	0918 510 5324 001			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7324 001	0918 514 6324 001	0918 514 5324 001			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7324 001	0918 516 6324 001	0918 516 5324 001			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7324 001	0918 520 6324 001	0918 520 5324 001			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7324 001	0918 526 6324 001	0918 526 5324 001			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7324 001	0918 530 6324 001	0918 530 5324 001			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7324 001	0918 534 6324 001	0918 534 5324 001			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7324 001	0918 540 6324 001	0918 540 5324 001			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7324 001	0918 550 6324 001	0918 550 5324 001			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7324 001	0918 560 6324 001	0918 560 5324 001			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7324 001	0918 564 6324 001	0918 564 5324 001			89,3	86,44	2,54 x 31 = 78,74	
D	06	0918 506 7322	0918 506 6322	0918 506 5322	Grey	4,5mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7322	0918 510 6322	0918 510 5322			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7322	0918 514 6322	0918 514 5322			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7322	0918 516 6322	0918 516 5322			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7322	0918 520 6322	0918 520 5322			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7322	0918 526 6322	0918 526 5322			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7322	0918 530 6322	0918 530 5322			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7322	0918 534 6322	0918 534 5322			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7322	0918 540 6322	0918 540 5322			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7322	0918 550 6322	0918 550 5322			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7322	0918 560 6322	0918 560 5322			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7322	0918 564 6322	0918 564 5322			89,3	86,44	2,54 x 31 = 78,74	
E	06	0918 506 7322 001	0918 506 6322 001	0918 506 5322 001	Black	4,5mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7322 001	0918 510 6322 001	0918 510 5322 001			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7322 001	0918 514 6322 001	0918 514 5322 001			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7322 001	0918 516 6322 001	0918 516 5322 001			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7322 001	0918 520 6322 001	0918 520 5322 001			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7322 001	0918 526 6322 001	0918 526 5322 001			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7322 001	0918 530 6322 001	0918 530 5322 001			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7322 001	0918 534 6322 001	0918 534 5322 001			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7322 001	0918 540 6322 001	0918 540 5322 001			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7322 001	0918 550 6322 001	0918 550 5322 001			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7322 001	0918 560 6322 001	0918 560 5322 001			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7322 001	0918 564 6322 001	0918 564 5322 001			89,3	86,44	2,54 x 31 = 78,74	
F	 All Dimensions in mm Original Size DIN A4		Scale 1:1	Free size tol.		Ref.				
	 All rights reserved Department EC PD - FR HARTING Electronics GmbH D-32339 Espelkamp		Created by DOUGE		Inspected by BAGDIKIAN		Date 2013-11-04		State Final Release	
			Title SEK 18 male straight low profile						Doc-Key / ECM-Nr. 100541601/UGD/001/B 500000066836	
			Type TB		Number 09185XXX32X				Rev. B	