

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


QUICKNET
TERMINATION TYPE
FIRE RATING
CAT LEVEL
CABLE OPTIONS
END 1 OPTIONS
JACK COLOR
TERMINATION TYPE
JACK COLOR
END 2 OPTIONS
ASSEMBLY OPTIONS
LABEL OPTIONS
LENGTH OPTIONS
Q C R B C R P X P L 150

QUICKNET PRE-TERMINATED SOLUTION	PERFORMANCE LEVEL	FIRE RATING	CABLE COLOR	END 1 OPTIONS		END 2 OPTIONS		ASSEMBLY OPTIONS	LABEL OPTIONS	LENGTH OPTIONS	OVERWRAP OPTIONS
				TERMINATION TYPE	JACK COLOR	TERMINATION TYPE	JACK COLOR				
Q (OK) QUICKNET KEYED JACKS	A-UTP CAT 6A B-UTP CAT 6e C-UTP CAT 6 D-UTP CAT 5e E-STP CAT6A U/FTP F-STP CAT 6 JACKS H-SHIELDED CAT6A S/FTP (IEEA ONLY) I-SHIELDED CAT6A S/FTP (IEEA ONLY) J-SHIELDED CAT6A F/UTP (IEEA ONLY) K-SHIELDED CAT6A S/FTP (IEEA ONLY) L-SHIELDED CAT6 F/UTP (IEEA ONLY) N-UTP CAT6A 3 CABLE LOOM O-UTP CAT6A 2 CABLE LOOM P-UTP CAT6A 4-WAY Q-UTP CAT6e 4-WAY R-UTP CAT 6 4-WAY S-UTP CAT 5e 4-WAY T-UTP CAT6A U/FTP U-STP CAT6A PATCH CORD CABLE V-UTP CAT6A PATCH CORD CABLE X-UTP CAT6A SD MATRIX CABLE Y- Z-UTP CAT6A MATRIX CABLE	P-PLENUM R-RISER L-LSZH C-CM	B-BLUE W-WHITE G-GREEN Y-YELLOW R-RED I-INT. GRAY L-BLACK O-ORANGE D-DARK GRAY	C-CASSETTE J-JACK NO STAGGER L-JACK STAGGER LT. K-JACK STAGGER RT. P-PLUG NO STAGGER S-PLUG STAGGER LT. O-PLUG STAGGER RT. T-PLUG STAGGER RT. FOR CISCO SWITCH V-PLUG STAGGER LT. FOR CISCO SWITCH	A-ARCTIC WHITE(AW) H-OFF WHITE(IW) E-ELECTRIC IVORY W-WHITE(WH) I-INTERNATIONAL GRAY L-BLACK (FOR SHIELDED) O-ORANGE R-RED B-BLUE G-GREEN Y-YELLOW V-VIOLET X-IF NOT A JACK	C-CASSETTE J-JACK NO STAGGER L-JACK STAGGER LT. K-JACK STAGGER RT. M-MUTOA BOX N-JACKS W/CASSETTE IN SEPARATE BOX P-PLUG NO STAGGER S-PLUG STAGGER LT. O-PLUG STAGGER RT. O-UN-TERMINATED WITH OPTIONAL CASSETTE AND JACKS U-UN-TERMINATED T-PLUG STAGGER RT. FOR CISCO SWITCH V-PLUG STAGGER LT. FOR CISCO SWITCH A-6 SIX PACK PLUG F-RECESSED PLUG PACK	A-ARTIC WHITE(AW) H-OFF WHITE(IW) E-ELECTRIC IVORY W-WHITE(WH) I-INTERNATIONAL GRAY L-BLACK (FOR SHIELDED) O-ORANGE R-RED B-BLUE G-GREEN Y-YELLOW V-VIOLET X-IF NOT A JACK B-BLUE PACK L-BLACK PACK R-RED PACK W-WHITE PACK	P-PULLING EYE (WILL APPEAR IF UN-TERMINATED, JACK, PLUG OR PLUG PACK) X-NO LOOM OPTIONS S-TSB 155 INTERNAL TESTING ONLY A-TSB6A TERMINATION FOR CAT6 & 6A	B-BOTH CUSTOM LOOM AND CABLE LOOMS C-CUSTOM CABLE LABEL UP TO 15 CHARACTERS L-CUSTOM LOOM LABEL UP TO 18 CHARACTERS X-NO CUSTOM LABELS	10-295 FT. INCREMENTS OF ONE FOOT 3M-90M IF IN METERS, NUMBER SHOWN AS LENGTH IS FOLLOWED BY "M" EXAMPLE: 90 METERS IS 90M PLACE A "0" AFTER THE "M" TO INDICATE ZERO ADDITIONAL LENGTH. PLACE A "5" AFTER THE "M" TO INDICATE 0.5M ADDITIONAL LENGTH. I.E.: 90M: 90 METERS LONG 90M5: 90.5 METERS LONG	BLANK-LOOMED T-TAK-TY E-EXPANDABLE SLEEVING
				IF KEYED (OK) SOLUTION FOR TERMINATION 2 COLORS ARE:		IF KEYED (OK) SOLUTION FOR TERMINATION 2 COLORS ARE:					
				1-BLACK 2-RED 3-GREEN 4-YELLOW 5-ORANGE 6-BLUE		1-BLACK 2-RED 3-GREEN 4-YELLOW 5-ORANGE 6-BLUE					



*NOTE: THE LENGTH OPTIONS
FOR THE SD TYPE PRODUCTS
I.E., OX____, WILL BE 10-
195 FT (3-60M)

*CONSULT FACTORY FOR AVAILABLE CONFIGURATIONS

I	4-1-10	BJN	CEF	SEE SHEET 1 FOR CHANGES.	02582-34	CEF		CEF	CEF	DRAWN BY MDJr	REVIEW DRAWING NUMBERS	PART NO. SEE TABLES
R	3-18-08	MDJr	WFM1	SEE SHEET 1 FOR CHANGES.	02582-34		TRW			DATE 12-14-06	MAT'L	DRAWING NO. 02582-34 SHEET 3 OF 3
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D WFM1		



PLUG PACK OPTION
(END 2 ONLY)



PULLING EYE OPTION
(END 2 ONLY)

MODEL FILENAME		SIZE
DRAWING FILENAME		A
M02582CG_DC34/00C		
QuickNet PRE-TERM CABLE ASSEMBLY CUSTOMER DRAWING		
PANDUITTM CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	
	PRODUCT SPEC/ PKG SPEC	
THIRD ANGLE PROJECTION	ASSY METHOD/ TEST METHOD	
	SCALE	
NONE		
PART NO.		SEE SHEET 3
DRAWING NO.		02582-34 SHEET 2 OF 3

I	4-1-10	BJN	CEF	SEE SHEET 1 FOR CHANGES.	02582-34	CEF		CEF	CEF
R	3-18-08	MDJr	WFM1	SEE SHEET 1 FOR CHANGES.	02582-34		TRW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[QCRBCBCBXX45](#)