





(1.27 mm) .050"

FFMD-20-T-02.00-01-N-R



FFMD-10-S-10.00-01



FFMD SERIES

TIGER EYE™ FLAT IDC WIRE CABLES

Mates with:

FLE*, SFMC*,

Transfer End Option

Mates with: FTS, FTSH,
EHF, SHF, ESHF

SPECIFICATIONS

For complete specifications
see www.samtec.com?FFMD

Insulator Material:

Black Glass Filled Polyester

Terminal:

Phosphor Bronze

Contact:

BeCu (-T)

Plating:

Sn over 50µ" (1.27 µm) Ni

Wire:

30 AWG

Current Rating:

2.5 A per pin

(1 pin powered)

Operating Temp Range:

-40°C to +105°C

Voltage Rating:

215 VAC

304 VDC

RoHS Compliant:

Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality


FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Other sizes
- Contact Samtec.

***Note:** Standard FFMD layout
will not mate with FLE, SFMC.
Must use gold plated callouts.
(See drawing on web.)
When mated with a socket,
Wire 1 mates with Pin 2;
Wire 2 mates with Pin 1, etc.

Note: This Series is
non-standard, non-returnable.



FFMD = Terminal Strip

