


Couplers Female

159-1618, 159-2215



Couplers Female



Dimensions: In.

SPECIFICATIONS	
Type:	vinyl insulated female disconnect
Material:	.016" thick brass
Nema tab:	.032" X .250"
Wire range:	22~16AWG (159-2215), 16~14AWG (159-1618)
Color:	red (159-2215), blue (159-1618)

Date Last Revised: 6-23-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300737

159-1618, 159-2215