



Wiha Quality Tools
Germany


Go To
Image Index

Go To
Numerical Index

22

Toll Free: (800) 494-6104

Wiha TORX® Protorn Screwdrivers



Through hardened for optimum wear resistance

Molded on ergonomic handle proportioned to blade sizes

High performance tool steel

Black finish blades



455 91 Set 6 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
455 91	455 06	T7 50	455 21	T10 80	.72
	455 11	T8 60	455 26	T15 80	
	455 16	T9 60	455 31	T20 100	

455 92 Set 8 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
455 92	455 11	T8 60	455 31	T20 100	1.07
	455 16	T9 60	455 36	T25 100	
	455 21	T10 80	455 41	T27 115	
	455 26	T15 80	455 46	T30 115	



455 89 Set 15 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
455 89	455 05	T6 50	455 31	T20 100	2.2
	455 06	T7 50	455 36	T25 100	
	455 11	T8 60	455 41	T27 115	
	455 16	T9 60	455 46	T30 115	
	455 21	T10 80	455 51	T40 130	
	455 22	T10 275	455 56	T45 130	
	455 26	T15 80	455 61	T50 130	
	455 28	T15 275			



484 00 1/4" Bit Holding Screwdriver, With Wiha-Protorn Handle

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Handle, molded on, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pcs.
484 00	1/4	125	5.0	243	9.6	.24	10



455 TORX® Screwdriver, With Wiha-Protorn Handle

Blade high alloy CVM steel, hardened, black finish. Molded on ergonomic Wiha-Protorn handle, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
455 05	T6	50	2.0	3.5	.139	129	5.1	.05	10
455 06	T7	50	2.0	3.5	.139	129	5.1	.05	10
455 11	T8	60	2.4	3.5	.139	139	5.5	.06	10
455 16	T9	60	2.4	4.0	.157	149	5.8	.08	10
455 21	T10	80	3.1	4.0	.157	170	6.7	.10	10
455 22	T10	275	10.8	4.0	.157	363	14.2	.13	10
455 26	T15	80	3.1	4.0	.157	170	6.7	.10	10
455 28	T15	275	10.8	4.0	.157	373	14.6	.15	10
455 31	T20	100	3.9	4.0	.157	190	7.5	.11	10
455 36	T25	100	3.9	4.5	.177	190	7.5	.11	10
455 41	T27	115	4.5	5.5	.216	215	8.4	.11	10
455 46	T30	115	4.5	6.0	.236	215	8.4	.20	10
455 51	T40	130	5.1	7.0	.275	240	9.4	.28	10
455 56	T45	130	5.1	8.0	.315	240	9.4	.27	10
455 61	T50	130	5.1	9.0	.354	240	9.4	.31	10

PREVIOUS

NEXT