

PART NAME	LARGE NON-METALLIC ENCLOSURE (STYLE C)				PART No.	NBC-10342	NBC-10352	NBC-10372	REV. DATE											
MATERIAL	FLAMMABILITY RATING	CONTINUOUS OPERATING TEMP.																		
ABS	UL94-HB	-40°C~+60°C/-40°F~140°F																		
ABS/PC BLEND	UL94-5VA	-40°C~+85°C/-40°F~185°F																		
PBT/PC BLEND	UL94-5VA + UV(f1)	-40°C~+75°C/-40°F~167°F																		
								<p><u>MATERIAL:</u> LATCHES, HINGES & PANEL BRACKETS _____ NON-METALLIC WALL MOUNTING BRACKETS _____ STAINLESS STEEL</p> <p><u>FINISH:</u> BODY, DOOR, LATCHES, HINGES & PANEL BRACKETS _____ LIGHT GRAY</p> <p><u>BOXES DESIGNED TO MEET STANDARDS:</u> UL508 TYPE 1, 2, 4, 4X INDOOR, 12 & 13 NEMA TYPE 1, 2, 4, 4X, 12 & 13 AND IEC529-IP66</p>												
								<p>AIR AND MOISTURE VENTS, STAINLESS STEEL LOCKING HASP, & GALVANIZED STEEL INTERNAL PANEL ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY.</p>												
<p><u>NOTE: ALL DIMENSIONS HAVE ± 0.039 [± 1] TOLERANCE UNLESS OTHERWISE SPECIFIED</u></p>																				
PART NO.	DIMENSIONS																			
INDOOR	INDOOR	OUTDOOR	A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	T	U
ABS	ABS/PC	PBT/PC	20.740	28.610	19.860	16.703	3.900	27.734	24.562	3.900	0.985	11.125	31.070	32.050	23.225	24.180	22.203	5.750	30.125	10.175
NBC-10342	NBC-10352	NBC-10372	[526.5]	[726.5]	[504]	[424]	[99]	[704]	[623.5]	[99]	[25]	[282]	[789]	[814]	[589.5]	[614]	[563.5]	[146]	[765]	[258]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[NBC-10352](#) [NBC-10372](#)