





Dimensions: mm (In.)




Schematic




PCB Hole Detail

102-1501



Schematic



PCB Hole Detail

102-1502

Electrical Specifications:

- Rating: .3A/30VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: > 100MΩ @ 500VDC
- Dielectric Strength: 500VAC for 1 Minute
- Electrical Life: 10,000 Cycles

Mechanical Specifications:

- Mechanical Life: 30,000 Cycles
- Operating Force: 200±150gF

Soldering Process:

- Temperature: 255°C max. 5 seconds

Mouser Stock No.	Type	Circuit
102-1501	DPDT	On-On
102-1502	DPDT	On-None-On

Slide Switches
102-1501, 102-1502

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[102-1502](#)