


FWJ-08-01-T-S



FWJ-05-02-T-S-RA



JW-13-04-T-S-550-150

(3,96 mm) .156"

FWJ, HFWJ, JW SERIES

POWER HEADERS & BOARD STACKERS

Mates with:
FHP

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FWJ or www.samtec.com?HFWJ

Insulator Material:

FWJ = Black Glass Filled Polyester
HFWJ = Natural Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn over 50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +105°C

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,20 mm) .008" max (02-16)

(0,25 mm) .010" max (17-24)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

TYPE STRIP

NO. OF PINS

LEAD STYLE

PLATING OPTION

S

OTHER OPTION


FWJ
= Standard HeaderHFWJ
= High Temp Header

FHP/HFWJ	
PINS	CURRENT RATING (PER CONTACT)
1	13.1 A
2	11.2 A
3	10.3 A
4	9.2 A
ALL	6.7 A

-T
= Matte Tin

Note: Some lengths, styles and options are non-standard, non-returnable.

01 thru 24



Specify LEAD STYLE from chart below.

LEAD STYLE	A	B	LEAD STYLE	C	LEAD STYLE	D	E	F
-01	(11,43) .450	(4,45) .175	-01	(10,46) .412	-01	(4,45) .175	(8,13) .320	(2,54) .100
-02	(12,70) .500		-02	(11,73) .462	-02	(3,96) .156	(13,56) .534	(4,95) .195
-04	(20,55) .809	(3,96) .156	-04	(19,10) .752	-04			
*-05	(3,81) .150	(12,07) .475						

*FWJ Only

Leave blank for Through-hole

-RA
= Right Angle (Style -02 & -04 only)-VS
= Surface Mount Requires HFWJ (2 pins/row minimum) Style -05 not available.-P
= Pick & Place Pad (3 Pos. min.) (6,98 mm) .275" min. post height (-VS only)

Mates with:
FHP

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?JW

Insulator Material:

Natural Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn over 50µ" (1,27 µm) Ni

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable: Yes

SMT Lead Coplanarity:

(0,20 mm) .008" max (02-16)

(0,25 mm) .010" max (17-24)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

JW

NO. OF PINS

04

PLATING OPTION

S

STACK HEIGHT

POST HEIGHT

OTHER OPTION

Note: This Series is non-standard, non-returnable.

-T
= Matte Tin


-“XXX”
= Stacker Height (in inches) (0,13 mm) .005" increments
Example: -250 = (6,35 mm) .250"

-“XXX”
= Post Height (in inches)

Leave blank for Through-hole

-VS
= Surface Mount (2 pins/row minimum)-P
= Pick & Place Pad (3 Pos. min.) (6,98 mm) .275" min. post height (-VS only)

02 thru 24



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685