

**Broadband Solutions**

CX3799714 | 2000040 EMPTY DUCT COEX

**ConQuest® Empty Conduit, 2 in, SCH 40, orange**

## Dimensions

Nominal Size	2 in
Wall Thickness Designation	SCH 40
Inner Diameter, nominal	51.994 mm   2.047 in
Length	762.00 m   2500.00 ft
Outer Diameter, nominal	60.325 mm   2.375 in
Wall Thickness, minimum	3.912 mm   0.154 in
Weight	472.0 lb/kft

## General Specifications

Color	Orange
Conduit Type	Non-toneable
Wall Type	Smooth
Brand	ConQuest®
Warranty	One year

## Material Specifications

Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm <sup>3</sup>
Density, minimum	0.941 g/cm <sup>3</sup>
Design Standard	ASTM D3350-05
Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B
Flexural Modulus, minimum	552 N/mm <sup>2</sup>   80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	21 N/mm <sup>2</sup>   3000 psi

## Mechanical Specifications

Minimum Bend Radius, unsupported	660.4 mm   26.0 in
----------------------------------	--------------------

# Product Specifications



CX3799714 | 2000040 EMPTY DUCT COEX

Pulling Tension, maximum 1043.3 kg | 2300.0 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance