



TSSH-115-01-L-D



TSSH-120-01-L-DH



(2,54 mm) .100"

TSSH SERIES

SHROUDED .025" SQ POST HEADERS

Mates with:

SSW, SSQ, SSM, SMSD

Important Note:

This Series will only mate with SSW, SSQ, SSM & SMSD Series

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/TSSH

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity (-DV):

(0,10 mm) .004" max (05-10)

(0,15 mm) .006" max (15-20)

(0,20 mm) .008" max (25-36)

SMT Lead Coplanarity (-DH):

(0,15 mm) .006" max


RECOGNITIONS

For complete scope of

recognitions see www.samtec.com/quality



APPLICATIONS



ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.

