


## PA / PAZ

### WIRE MARKING



### GENERAL INFORMATION

#### Design

Closed combination marker. Unique bellow design enables wide diameter range and permanent grip. A chevron cut prevents twisting between adjacent sleeves. The hot stamp print gives excellent legibility.

#### Colours

PA: Standard colours yellow and white and international colour code for 0-9.  
PAZ: Standard colours yellow and white. Other colours, please contact Partex.

#### Multi character marking

See separate product information.

- Closed, permanent grip and adjustable marking sleeve for as yet unconnected wires.
- For applications including electrical engineering, pneumatics and hydraulics.
- Twist-protection for secure combination marking
- Excellent legibility
- Available in halogen free material (Zerex)

### FACTS

#### Material:

PA: Cadmium and silicon free, soft PVC according to special Partex formula.  
PAZ: Zerex, thermoplastic polyether based polurethane mixture. The material is free from halogen, cadmium and silicon.

#### Printing:

PA: PVC, Hot stamped.  
PAZ: ZEREX, Etching black ink jet with high resolution

#### Text:

Alphanumeric and special characters.

#### Resistance:

The product is tested according to Partex Product Test Program by the Swedish Test and Research Institute and has the following test properties:

- Flammability resistance according to UL94-V0.
- Resistant to UV radiation, corresponding to 1 year outdoors in the south of Sweden.
- Resistance to chemicals meets Partex Product Test Program.
- Resistance to temperature and ageing meets norms of Partex Product Test Program.

For application in hostile environments, please contact Partex for information.

#### Temperature resistance:

PA: Shape permanence from -30°C to +60°C (-22°F to +140°F).  
PAZ: Shape permanence from -30°C to +90°C (-22°F to +194°F).

## PRODUCT AND ORDERING INFORMATION


### PA02



Diameter: 1.3 - 3.0 mm  
Area: ~0.2 - 1.5 mm<sup>2</sup>  
Inch: .051" - .118"  
Sleeve length: 3 mm

No# of characters: 1

ZEREX = Halogen free material  
# = Packaging



|                   | Article number<br>PVC | Article number<br>PVC | Article number<br>Zerex | Article number<br>Zerex | Article number<br>PVC |
|-------------------|-----------------------|-----------------------|-------------------------|-------------------------|-----------------------|
| Character         | Yellow                | White                 | Yellow                  | White                   | Colour code           |
| 0                 | PA-02003#V40.0        | PA-02003#V90.0        | PAZ02003SB40.0          | PAZ02003SB90.0          | PA-02003#V09.0        |
| 1                 | PA-02003#V40.1        | PA-02003#V90.1        | PAZ02003SB40.1          | PAZ02003SB90.1          | PA-02003#V19.1        |
| 2                 | PA-02003#V40.2        | PA-02003#V90.2        | PAZ02003SB40.2          | PAZ02003SB90.2          | PA-02003#V29.2        |
| 3                 | PA-02003#V40.3        | PA-02003#V90.3        | PAZ02003SB40.3          | PAZ02003SB90.3          | PA-02003#V30.3        |
| 4                 | PA-02003#V40.4        | PA-02003#V90.4        | PAZ02003SB40.4          | PAZ02003SB90.4          | PA-02003#V40.4        |
| 5                 | PA-02003#V40.5        | PA-02003#V90.5        | PAZ02003SB40.5          | PAZ02003SB90.5          | PA-02003#V59.5        |
| 6                 | PA-02003#V40.6        | PA-02003#V90.6        | PAZ02003SB40.6          | PAZ02003SB90.6          | PA-02003#V69.6        |
| 7                 | PA-02003#V40.7        | PA-02003#V90.7        | PAZ02003SB40.7          | PAZ02003SB90.7          | PA-02003#V79.7        |
| 8                 | PA-02003#V40.8        | PA-02003#V90.8        | PAZ02003SB40.8          | PAZ02003SB90.8          | PA-02003#V80.8        |
| 9                 | PA-02003#V40.9        | PA-02003#V90.9        | PAZ02003SB40.9          | PAZ02003SB90.9          | PA-02003#V90.9        |
| A                 | PA-02003#V40.A        | PA-02003#V90.A        | PAZ02003SB40.A          | PAZ02003SB90.A          | -                     |
| B                 | PA-02003#V40.B        | PA-02003#V90.B        | PAZ02003SB40.B          | PAZ02003SB90.B          | -                     |
| C                 | PA-02003#V40.C        | PA-02003#V90.C        | PAZ02003SB40.C          | PAZ02003SB90.C          | -                     |
| D                 | PA-02003#V40.D        | PA-02003#V90.D        | PAZ02003SB40.D          | PAZ02003SB90.D          | -                     |
| E                 | PA-02003#V40.E        | PA-02003#V90.E        | PAZ02003SB40.E          | PAZ02003SB90.E          | -                     |
| F                 | PA-02003#V40.F        | PA-02003#V90.F        | PAZ02003SB40.F          | PAZ02003SB90.F          | -                     |
| G                 | PA-02003#V40.G        | PA-02003#V90.G        | PAZ02003SB40.G          | PAZ02003SB90.G          | -                     |
| H                 | PA-02003#V40.H        | PA-02003#V90.H        | PAZ02003SB40.H          | PAZ02003SB90.H          | -                     |
| I                 | PA-02003#V40.I        | PA-02003#V90.I        | PAZ02003SB40.I          | PAZ02003SB90.I          | -                     |
| J                 | PA-02003#V40.J        | PA-02003#V90.J        | PAZ02003SB40.J          | PAZ02003SB90.J          | -                     |
| K                 | PA-02003#V40.K        | PA-02003#V90.K        | PAZ02003SB40.K          | PAZ02003SB90.K          | -                     |
| L                 | PA-02003#V40.L        | PA-02003#V90.L        | PAZ02003SB40.L          | PAZ02003SB90.L          | -                     |
| M                 | PA-02003#V40.M        | PA-02003#V90.M        | PAZ02003SB40.M          | PAZ02003SB90.M          | -                     |
| N                 | PA-02003#V40.N        | PA-02003#V90.N        | PAZ02003SB40.N          | PAZ02003SB90.N          | -                     |
| O                 | PA-02003#V40.O        | PA-02003#V90.O        | PAZ02003SB40.O          | PAZ02003SB90.O          | -                     |
| P                 | PA-02003#V40.P        | PA-02003#V90.P        | PAZ02003SB40.P          | PAZ02003SB90.P          | -                     |
| Q                 | PA-02003#V40.Q        | PA-02003#V90.Q        | PAZ02003SB40.Q          | PAZ02003SB90.Q          | -                     |
| R                 | PA-02003#V40.R        | PA-02003#V90.R        | PAZ02003SB40.R          | PAZ02003SB90.R          | -                     |
| S                 | PA-02003#V40.S        | PA-02003#V90.S        | PAZ02003SB40.S          | PAZ02003SB90.S          | -                     |
| T                 | PA-02003#V40.T        | PA-02003#V90.T        | PAZ02003SB40.T          | PAZ02003SB90.T          | -                     |
| U                 | PA-02003#V40.U        | PA-02003#V90.U        | PAZ02003SB40.U          | PAZ02003SB90.U          | -                     |
| V                 | PA-02003#V40.V        | PA-02003#V90.V        | PAZ02003SB40.V          | PAZ02003SB90.V          | -                     |
| W                 | PA-02003#V40.W        | PA-02003#V90.W        | PAZ02003SB40.W          | PAZ02003SB90.W          | -                     |
| X                 | PA-02003#V40.X        | PA-02003#V90.X        | PAZ02003SB40.X          | PAZ02003SB90.X          | -                     |
| Y                 | PA-02003#V40.Y        | PA-02003#V90.Y        | PAZ02003SB40.Y          | PAZ02003SB90.Y          | -                     |
| Z                 | PA-02003#V40.Z        | PA-02003#V90.Z        | PAZ02003SB40.Z          | PAZ02003SB90.Z          | -                     |
| Å                 | PA-02003#V40.Å        | PA-02003#V90.Å        | PAZ02003SB40.Å          | PAZ02003SB90.Å          | -                     |
| Ä                 | PA-02003#V40.Ä        | PA-02003#V90.Ä        | PAZ02003SB40.Ä          | PAZ02003SB90.Ä          | -                     |
| Ö                 | PA-02003#V40.Ö        | PA-02003#V90.Ö        | PAZ02003SB40.Ö          | PAZ02003SB90.Ö          | -                     |
| +                 | PA-02003#V40.+        | PA-02003#V90.+        | PAZ02003SB40.+          | PAZ02003SB90.+          | -                     |
| -                 | PA-02003#V40.-        | PA-02003#V90.-        | PAZ02003SB40.-          | PAZ02003SB90.-          | -                     |
| .                 | PA-02003#V40..        | PA-02003#V90..        | PAZ02003SB40..          | PAZ02003SB90..          | -                     |
| /                 | PA-02003#V40./        | PA-02003#V90./        | PAZ02003SB40./          | PAZ02003SB90./          | -                     |
| :                 | PA-02003#V40.:        | PA-02003#V90.:        | PAZ02003SB40.:          | PAZ02003SB90.;          | -                     |
| =                 | PA-02003#V40.EQ       | PA-02003#V90.EQ       | PAZ02003SB40.EQ         | PAZ02003SB90.EQ         | -                     |
| Earth             | PA-02003#V40.GRD      | PA-02003#V90.GRD      | -                       | -                       | -                     |
| Earth in a Circle | PA-02003#V40.GRDC     | PA-02003#V90.GRDC     | -                       | -                       | -                     |
| "Neutral/Blank"   | PA-02003#N4           | PA-02003#N9           | PAZ02003SN4             | PAZ02003SN9             | -                     |

### PACKAGING



#### Compact disc

Number of markers: 500 pcs

Packaging: S

Example: PA-02003SV40.0



#### Reel

Number of markers: 1000 pcs

Packaging: B

Example: PA-02003BV40.0



#### Single bag

Number of markers: 10x25 pcs

Packaging: P

Example: PA-02003PV40.0



#### Strip pack

Number of markers: 5x200 pcs

Packaging: A

Example: PA-02003AV40.0

## PRODUCT AND ORDERING INFORMATION


### PA 1



Diameter: 2.5 - 5.0 mm  
Area: ~1.5 - 4.0 mm<sup>2</sup>  
Inch: .059" - .197"  
Sleeve length: 3 mm

No# of characters: 1

ZEREX = Halogen free material  
# = Packaging



|                   | Article number<br>PVC | Article number<br>PVC | Article number<br>Zerex | Article number<br>Zerex | Article number<br>PVC |
|-------------------|-----------------------|-----------------------|-------------------------|-------------------------|-----------------------|
| Character         | Yellow                | White                 | Yellow                  | White                   | Colour code           |
| 0                 | PA-10003#V40.0        | PA-10003#V90.0        | PAZ10003SB40.0          | PAZ10003SB90.0          | PA-10003#V09.0        |
| 1                 | PA-10003#V40.1        | PA-10003#V90.1        | PAZ10003SB40.1          | PAZ10003SB90.1          | PA-10003#V19.1        |
| 2                 | PA-10003#V40.2        | PA-10003#V90.2        | PAZ10003SB40.2          | PAZ10003SB90.2          | PA-10003#V29.2        |
| 3                 | PA-10003#V40.3        | PA-10003#V90.3        | PAZ10003SB40.3          | PAZ10003SB90.3          | PA-10003#V30.3        |
| 4                 | PA-10003#V40.4        | PA-10003#V90.4        | PAZ10003SB40.4          | PAZ10003SB90.4          | PA-10003#V40.4        |
| 5                 | PA-10003#V40.5        | PA-10003#V90.5        | PAZ10003SB40.5          | PAZ10003SB90.5          | PA-10003#V59.5        |
| 6                 | PA-10003#V40.6        | PA-10003#V90.6        | PAZ10003SB40.6          | PAZ10003SB90.6          | PA-10003#V69.6        |
| 7                 | PA-10003#V40.7        | PA-10003#V90.7        | PAZ10003SB40.7          | PAZ10003SB90.7          | PA-10003#V79.7        |
| 8                 | PA-10003#V40.8        | PA-10003#V90.8        | PAZ10003SB40.8          | PAZ10003SB90.8          | PA-10003#V80.8        |
| 9                 | PA-10003#V40.9        | PA-10003#V90.9        | PAZ10003SB40.9          | PAZ10003SB90.9          | PA-10003#V90.9        |
| A                 | PA-10003#V40.A        | PA-10003#V90.A        | PAZ10003SB40.A          | PAZ10003SB90.A          | -                     |
| B                 | PA-10003#V40.B        | PA-10003#V90.B        | PAZ10003SB40.B          | PAZ10003SB90.B          | -                     |
| C                 | PA-10003#V40.C        | PA-10003#V90.C        | PAZ10003SB40.C          | PAZ10003SB90.C          | -                     |
| D                 | PA-10003#V40.D        | PA-10003#V90.D        | PAZ10003SB40.D          | PAZ10003SB90.D          | -                     |
| E                 | PA-10003#V40.E        | PA-10003#V90.E        | PAZ10003SB40.E          | PAZ10003SB90.E          | -                     |
| F                 | PA-10003#V40.F        | PA-10003#V90.F        | PAZ10003SB40.F          | PAZ10003SB90.F          | -                     |
| G                 | PA-10003#V40.G        | PA-10003#V90.G        | PAZ10003SB40.G          | PAZ10003SB90.G          | -                     |
| H                 | PA-10003#V40.H        | PA-10003#V90.H        | PAZ10003SB40.H          | PAZ10003SB90.H          | -                     |
| I                 | PA-10003#V40.I        | PA-10003#V90.I        | PAZ10003SB40.I          | PAZ10003SB90.I          | -                     |
| J                 | PA-10003#V40.J        | PA-10003#V90.J        | PAZ10003SB40.J          | PAZ10003SB90.J          | -                     |
| K                 | PA-10003#V40.K        | PA-10003#V90.K        | PAZ10003SB40.K          | PAZ10003SB90.K          | -                     |
| L                 | PA-10003#V40.L        | PA-10003#V90.L        | PAZ10003SB40.L          | PAZ10003SB90.L          | -                     |
| M                 | PA-10003#V40.M        | PA-10003#V90.M        | PAZ10003SB40.M          | PAZ10003SB90.M          | -                     |
| N                 | PA-10003#V40.N        | PA-10003#V90.N        | PAZ10003SB40.N          | PAZ10003SB90.N          | -                     |
| O                 | PA-10003#V40.O        | PA-10003#V90.O        | PAZ10003SB40.O          | PAZ10003SB90.O          | -                     |
| P                 | PA-10003#V40.P        | PA-10003#V90.P        | PAZ10003SB40.P          | PAZ10003SB90.P          | -                     |
| Q                 | PA-10003#V40.Q        | PA-10003#V90.Q        | PAZ10003SB40.Q          | PAZ10003SB90.Q          | -                     |
| R                 | PA-10003#V40.R        | PA-10003#V90.R        | PAZ10003SB40.R          | PAZ10003SB90.R          | -                     |
| S                 | PA-10003#V40.S        | PA-10003#V90.S        | PAZ10003SB40.S          | PAZ10003SB90.S          | -                     |
| T                 | PA-10003#V40.T        | PA-10003#V90.T        | PAZ10003SB40.T          | PAZ10003SB90.T          | -                     |
| U                 | PA-10003#V40.U        | PA-10003#V90.U        | PAZ10003SB40.U          | PAZ10003SB90.U          | -                     |
| V                 | PA-10003#V40.V        | PA-10003#V90.V        | PAZ10003SB40.V          | PAZ10003SB90.V          | -                     |
| W                 | PA-10003#V40.W        | PA-10003#V90.W        | PAZ10003SB40.W          | PAZ10003SB90.W          | -                     |
| X                 | PA-10003#V40.X        | PA-10003#V90.X        | PAZ10003SB40.X          | PAZ10003SB90.X          | -                     |
| Y                 | PA-10003#V40.Y        | PA-10003#V90.Y        | PAZ10003SB40.Y          | PAZ10003SB90.Y          | -                     |
| Z                 | PA-10003#V40.Z        | PA-10003#V90.Z        | PAZ10003SB40.Z          | PAZ10003SB90.Z          | -                     |
| Ä                 | PA-10003#V40.Ä        | PA-10003#V90.Ä        | PAZ10003SB40.Ä          | PAZ10003SB90.Ä          | -                     |
| Å                 | PA-10003#V40.Å        | PA-10003#V90.Å        | PAZ10003SB40.Å          | PAZ10003SB90.Å          | -                     |
| Ö                 | PA-10003#V40.Ö        | PA-10003#V90.Ö        | PAZ10003SB40.Ö          | PAZ10003SB90.Ö          | -                     |
| +                 | PA-10003#V40.+        | PA-10003#V90.+        | PAZ10003SB40.+          | PAZ10003SB90.+          | -                     |
| -                 | PA-10003#V40.-        | PA-10003#V90.-        | PAZ10003SB40.-          | PAZ10003SB90.-          | -                     |
| .                 | PA-10003#V40..        | PA-10003#V90..        | PAZ10003SB40..          | PAZ10003SB90..          | -                     |
| /                 | PA-10003#V40./        | PA-10003#V90./        | PAZ10003SB40./          | PAZ10003SB90./          | -                     |
| :                 | PA-10003#V40.:        | PA-10003#V90.:        | PAZ10003SB40.:          | PAZ10003SB90.:          | -                     |
| =                 | PA-10003#V40.EQ       | PA-10003#V90.EQ       | PAZ10003SB40.EQ         | PAZ10003SB90.EQ         | -                     |
| Earth             | PA-10003#V40.GRD      | PA-10003#V90.GRD      | -                       | -                       | -                     |
| Earth in a Circle | PA-10003#V40.GRDC     | PA-10003#V90.GRDC     | -                       | -                       | -                     |
| "Neutral/Blank"   | PA-10003#N4           | PA-10003#N9           | PAZ10003SN4             | PAZ10003SN9             | -                     |

### PACKAGING



**Compact disc**  
Number of markers: 500 pcs  
Packaging: S  
Example: PA-10003SV40.0



**Reel**  
Number of markers: 1000 pcs  
Packaging: B  
Example: PA-10003BV40.0



**Single bag**  
Number of markers: 10x25 pcs  
Packaging: P  
Example: PA-10003PV40.0



**Strip pack**  
Number of markers: 5x200 pcs  
Packaging: A  
Example: PA-10003AV40.0

# PRODUCT AND ORDERING INFORMATION


## PA2



Diameter: 4.0 - 10.0 mm  
 Area: ~2.5 - 16.0 mm<sup>2</sup>  
 Inch: .157" - .394"  
 Sleeve length: 4 mm

No# of characters: 1

ZEREX = Halogen free material  
 # = Packaging



|                   | Article number<br>PVC | Article number<br>PVC | Article number<br>Zerex | Article number<br>Zerex | Article number<br>PVC |
|-------------------|-----------------------|-----------------------|-------------------------|-------------------------|-----------------------|
| Character         | Yellow                | White                 | Yellow                  | White                   | Colour code           |
| 0                 | PA-20004#V40.0        | PA-20004#V90.0        | PAZ20004SB40.0          | PAZ20004SB90.0          | PA-20004#V09.0        |
| 1                 | PA-20004#V40.1        | PA-20004#V90.1        | PAZ20004SB40.1          | PAZ20004SB90.1          | PA-20004#V19.1        |
| 2                 | PA-20004#V40.2        | PA-20004#V90.2        | PAZ20004SB40.2          | PAZ20004SB90.2          | PA-20004#V29.2        |
| 3                 | PA-20004#V40.3        | PA-20004#V90.3        | PAZ20004SB40.3          | PAZ20004SB90.3          | PA-20004#V30.3        |
| 4                 | PA-20004#V40.4        | PA-20004#V90.4        | PAZ20004SB40.4          | PAZ20004SB90.4          | PA-20004#V40.4        |
| 5                 | PA-20004#V40.5        | PA-20004#V90.5        | PAZ20004SB40.5          | PAZ20004SB90.5          | PA-20004#V59.5        |
| 6                 | PA-20004#V40.6        | PA-20004#V90.6        | PAZ20004SB40.6          | PAZ20004SB90.6          | PA-20004#V69.6        |
| 7                 | PA-20004#V40.7        | PA-20004#V90.7        | PAZ20004SB40.7          | PAZ20004SB90.7          | PA-20004#V79.7        |
| 8                 | PA-20004#V40.8        | PA-20004#V90.8        | PAZ20004SB40.8          | PAZ20004SB90.8          | PA-20004#V80.8        |
| 9                 | PA-20004#V40.9        | PA-20004#V90.9        | PAZ20004SB40.9          | PAZ20004SB90.9          | PA-20004#V90.9        |
| A                 | PA-20004#V40.A        | PA-20004#V90.A        | PAZ20004SB40.A          | PAZ20004SB90.A          | -                     |
| B                 | PA-20004#V40.B        | PA-20004#V90.B        | PAZ20004SB40.B          | PAZ20004SB90.B          | -                     |
| C                 | PA-20004#V40.C        | PA-20004#V90.C        | PAZ20004SB40.C          | PAZ20004SB90.C          | -                     |
| D                 | PA-20004#V40.D        | PA-20004#V90.D        | PAZ20004SB40.D          | PAZ20004SB90.D          | -                     |
| E                 | PA-20004#V40.E        | PA-20004#V90.E        | PAZ20004SB40.E          | PAZ20004SB90.E          | -                     |
| F                 | PA-20004#V40.F        | PA-20004#V90.F        | PAZ20004SB40.F          | PAZ20004SB90.F          | -                     |
| G                 | PA-20004#V40.G        | PA-20004#V90.G        | PAZ20004SB40.G          | PAZ20004SB90.G          | -                     |
| H                 | PA-20004#V40.H        | PA-20004#V90.H        | PAZ20004SB40.H          | PAZ20004SB90.H          | -                     |
| I                 | PA-20004#V40.I        | PA-20004#V90.I        | PAZ20004SB40.I          | PAZ20004SB90.I          | -                     |
| J                 | PA-20004#V40.J        | PA-20004#V90.J        | PAZ20004SB40.J          | PAZ20004SB90.J          | -                     |
| K                 | PA-20004#V40.K        | PA-20004#V90.K        | PAZ20004SB40.K          | PAZ20004SB90.K          | -                     |
| L                 | PA-20004#V40.L        | PA-20004#V90.L        | PAZ20004SB40.L          | PAZ20004SB90.L          | -                     |
| M                 | PA-20004#V40.M        | PA-20004#V90.M        | PAZ20004SB40.M          | PAZ20004SB90.M          | -                     |
| N                 | PA-20004#V40.N        | PA-20004#V90.N        | PAZ20004SB40.N          | PAZ20004SB90.N          | -                     |
| O                 | PA-20004#V40.O        | PA-20004#V90.O        | PAZ20004SB40.O          | PAZ20004SB90.O          | -                     |
| P                 | PA-20004#V40.P        | PA-20004#V90.P        | PAZ20004SB40.P          | PAZ20004SB90.P          | -                     |
| Q                 | PA-20004#V40.Q        | PA-20004#V90.Q        | PAZ20004SB40.Q          | PAZ20004SB90.Q          | -                     |
| R                 | PA-20004#V40.R        | PA-20004#V90.R        | PAZ20004SB40.R          | PAZ20004SB90.R          | -                     |
| S                 | PA-20004#V40.S        | PA-20004#V90.S        | PAZ20004SB40.S          | PAZ20004SB90.S          | -                     |
| T                 | PA-20004#V40.T        | PA-20004#V90.T        | PAZ20004SB40.T          | PAZ20004SB90.T          | -                     |
| U                 | PA-20004#V40.U        | PA-20004#V90.U        | PAZ20004SB40.U          | PAZ20004SB90.U          | -                     |
| V                 | PA-20004#V40.V        | PA-20004#V90.V        | PAZ20004SB40.V          | PAZ20004SB90.V          | -                     |
| W                 | PA-20004#V40.W        | PA-20004#V90.W        | PAZ20004SB40.W          | PAZ20004SB90.W          | -                     |
| X                 | PA-20004#V40.X        | PA-20004#V90.X        | PAZ20004SB40.X          | PAZ20004SB90.X          | -                     |
| Y                 | PA-20004#V40.Y        | PA-20004#V90.Y        | PAZ20004SB40.Y          | PAZ20004SB90.Y          | -                     |
| Z                 | PA-20004#V40.Z        | PA-20004#V90.Z        | PAZ20004SB40.Z          | PAZ20004SB90.Z          | -                     |
| Å                 | PA-20004#V40.Å        | PA-20004#V90.Å        | PAZ20004SB40.Å          | PAZ20004SB90.Å          | -                     |
| Ä                 | PA-20004#V40.Ä        | PA-20004#V90.Ä        | PAZ20004SB40.Ä          | PAZ20004SB90.Ä          | -                     |
| Ö                 | PA-20004#V40.Ö        | PA-20004#V90.Ö        | PAZ20004SB40.Ö          | PAZ20004SB90.Ö          | -                     |
| +                 | PA-20004#V40.+        | PA-20004#V90.+        | PAZ20004SB40.+          | PAZ20004SB90.+          | -                     |
| -                 | PA-20004#V40.-        | PA-20004#V90.-        | PAZ20004SB40.-          | PAZ20004SB90.-          | -                     |
| .                 | PA-20004#V40..        | PA-20004#V90..        | PAZ20004SB40..          | PAZ20004SB90..          | -                     |
| /                 | PA-20004#V40./        | PA-20004#V90./        | PAZ20004SB40./          | PAZ20004SB90./          | -                     |
| :                 | PA-20004#V40.:        | PA-20004#V90.:        | PAZ20004SB40.:          | PAZ20004SB90.:          | -                     |
| =                 | PA-20004#V40.EQ       | PA-20004#V90.EQ       | PAZ20004SB40.EQ         | PAZ20004SB90.EQ         | -                     |
| Earth             | PA-20004#V40.GRD      | PA-20004#V90.GRD      | -                       | -                       | -                     |
| Earth in a Circle | PA-20004#V40.GRDC     | PA-20004#V90.GRDC     | -                       | -                       | -                     |
| "Neutral/Blank"   | PA-20004#N4           | PA-20004#N9           | PAZ20004SN4             | PAZ20004SN9             | -                     |

## PACKAGING



**Compact disc**  
 Number of markers: 250 pcs  
 Packaging: S  
 Example: PA-20004SV40.0




**Strip pack**  
 Number of markers: 5x100 pcs  
 Packaging: A  
 Example: PA-20004AV40.0

# PRODUCT AND ORDERING INFORMATION

## PA3



Diameter: 8.0 - 16.0 mm  
 Area: ~16.0 - 70.0 mm<sup>2</sup>  
 Inch: .315" - .630"  
 Sleeve length: 6 mm  
 No# of characters: 1



|                   | Article number<br>PVC | Article number<br>PVC | Article number<br>Zerex | Article number<br>Zerex | Article number<br>PVC |
|-------------------|-----------------------|-----------------------|-------------------------|-------------------------|-----------------------|
| Character         | Yellow                | White                 | Yellow                  | White                   | Yellow                |
| 0                 | PA-30006AV40.0        | PA-30006AV90.0        | -                       | -                       | -                     |
| 1                 | PA-30006AV40.1        | PA-30006AV90.1        | -                       | -                       | -                     |
| 2                 | PA-30006AV40.2        | PA-30006AV90.2        | -                       | -                       | -                     |
| 3                 | PA-30006AV40.3        | PA-30006AV90.3        | -                       | -                       | -                     |
| 4                 | PA-30006AV40.4        | PA-30006AV90.4        | -                       | -                       | -                     |
| 5                 | PA-30006AV40.5        | PA-30006AV90.5        | -                       | -                       | -                     |
| 6                 | PA-30006AV40.6        | PA-30006AV90.6        | -                       | -                       | -                     |
| 7                 | PA-30006AV40.7        | PA-30006AV90.7        | -                       | -                       | -                     |
| 8                 | PA-30006AV40.8        | PA-30006AV90.8        | -                       | -                       | -                     |
| 9                 | PA-30006AV40.9        | PA-30006AV90.9        | -                       | -                       | -                     |
| A                 | PA-30006AV40.A        | PA-30006AV90.A        | -                       | -                       | -                     |
| B                 | PA-30006AV40.B        | PA-30006AV90.B        | -                       | -                       | -                     |
| C                 | PA-30006AV40.C        | PA-30006AV90.C        | -                       | -                       | -                     |
| D                 | PA-30006AV40.D        | PA-30006AV90.D        | -                       | -                       | -                     |
| E                 | PA-30006AV40.E        | PA-30006AV90.E        | -                       | -                       | -                     |
| F                 | PA-30006AV40.F        | PA-30006AV90.F        | -                       | -                       | -                     |
| G                 | PA-30006AV40.G        | PA-30006AV90.G        | -                       | -                       | -                     |
| H                 | PA-30006AV40.H        | PA-30006AV90.H        | -                       | -                       | -                     |
| I                 | PA-30006AV40.I        | PA-30006AV90.I        | -                       | -                       | -                     |
| J                 | PA-30006AV40.J        | PA-30006AV90.J        | -                       | -                       | -                     |
| K                 | PA-30006AV40.K        | PA-30006AV90.K        | -                       | -                       | -                     |
| L                 | PA-30006AV40.L        | PA-30006AV90.L        | -                       | -                       | -                     |
| M                 | PA-30006AV40.M        | PA-30006AV90.M        | -                       | -                       | -                     |
| N                 | PA-30006AV40.N        | PA-30006AV90.N        | -                       | -                       | -                     |
| O                 | PA-30006AV40.O        | PA-30006AV90.O        | -                       | -                       | -                     |
| P                 | PA-30006AV40.P        | PA-30006AV90.P        | -                       | -                       | -                     |
| Q                 | PA-30006AV40.Q        | PA-30006AV90.Q        | -                       | -                       | -                     |
| R                 | PA-30006AV40.R        | PA-30006AV90.R        | -                       | -                       | -                     |
| S                 | PA-30006AV40.S        | PA-30006AV90.S        | -                       | -                       | -                     |
| T                 | PA-30006AV40.T        | PA-30006AV90.T        | -                       | -                       | -                     |
| U                 | PA-30006AV40.U        | PA-30006AV90.U        | -                       | -                       | -                     |
| V                 | PA-30006AV40.V        | PA-30006AV90.V        | -                       | -                       | -                     |
| W                 | PA-30006AV40.W        | PA-30006AV90.W        | -                       | -                       | -                     |
| X                 | PA-30006AV40.X        | PA-30006AV90.X        | -                       | -                       | -                     |
| Y                 | PA-30006AV40.Y        | PA-30006AV90.Y        | -                       | -                       | -                     |
| Z                 | PA-30006AV40.Z        | PA-30006AV90.Z        | -                       | -                       | -                     |
| Å                 | PA-30006AV40.Å        | PA-30006AV90.Å        | -                       | -                       | -                     |
| Ä                 | PA-30006AV40.Ä        | PA-30006AV90.Ä        | -                       | -                       | -                     |
| Ö                 | PA-30006AV40.Ö        | PA-30006AV90.Ö        | -                       | -                       | -                     |
| +                 | PA-30006AV40.+        | PA-30006AV90.+        | -                       | -                       | -                     |
| -                 | PA-30006AV40.-        | PA-30006AV90.-        | -                       | -                       | -                     |
| .                 | PA-30006AV40..        | PA-30006AV90..        | -                       | -                       | -                     |
| /                 | PA-30006AV40./        | PA-30006AV90./        | -                       | -                       | -                     |
| :                 | PA-30006AV40.:        | PA-30006AV90.:        | -                       | -                       | -                     |
| =                 | PA-30006AV40.EQ       | PA-30006AV90.EQ       | -                       | -                       | -                     |
| Earth             | PA-30006AV40.GRD      | PA-30006AV90.GRD      | -                       | -                       | -                     |
| Earth in a Circle | PA-30006AV40.GRDC     | PA-30006AV90.GRDC     | -                       | -                       | -                     |
| "Neutral/Blank"   | PA-30004AN4           | PA-30006AN9           | -                       | -                       | -                     |


## PACKAGING



**Strip pack**  
 Number of markers: 5x20 pcs  
 Packaging: A  
 Example: PA-30006AV40.0


ACCESSORIES

PAD AND PAV INSTALLATION TOOLS




**PAD**  
Teflon coated stainless steel alt. stainless steel conical installation tool with axial hole at the fat end for wire. For use with striped wires an Partex wire marking PA02 and PA1.


**PAV**  
U-shaped installation tool in stainless steel for both left and right mounting. Depending on how the U-shaped part of PAV is turned in, the marker can be expanded over the whole diameter range.



| Tool  | Designed for | Length mm | Diameter |      | Inner diameter |      | Number /Pack. | Article number |               |
|-------|--------------|-----------|----------|------|----------------|------|---------------|----------------|---------------|
|       |              |           | mm       | Inch | mm             | Inch |               | Metal          | Teflon coatad |
| PAD-3 | PA02         | 100       | 3,1      | .122 | 1,8            | .70  | 1 pce         | PAD-3M         | PAD-3T        |
| PAD-4 | PA1          | 100       | 4,2      | .165 | 2.5            | .98  | 1 pce         | PAD-4M         | PAD-4T        |
| PAD-5 | PA1          | 100       | 5,0      | .197 | 2,5            | .98  | 1 pce         | PAD-5M         | PAD-5T        |
| PAV02 | PA02         | 124       | 3,8      | .150 | -              | -    | 1 pce         | PAV02M         |               |
| PAV10 | PA1          | 130       | 5,0      | .197 | -              | -    | 1 pce         | PAV03M         |               |



MD - MDH



CAS - PAM



SRP



PSK