



Belegungsplan
Loading-Plan
acc. EIA TIA 568A
Schirm Shield


1	Weiß(grün)	White(green)	1
2	grün	Green	2
3	Weiß(orange)	White(orange)	3
4	Blau	Blue	4
5	Weiß(blau)	White(blue)	5
6	Orange	Orange	6
7	Weiß(braun)	White(brown)	7
8	Braun	Brown	8



- Übertragungseigenschaften nach ISO/IEC 11801:2002: Class E.
- Schutzart: IP20
- Temperaturbereich: -40°C ... +70°C

- Transmission properties in accordance with ISO/IEC 11801:2002: Class E.
- Protection level: IP20
- Temperature range: -40°C ... +70°C

AWG 27/7 flexibel/stranded	09 45 751 1553	20 m
AWG 27/7 flexibel/stranded	09 45 751 1551	10 m
AWG 27/7 flexibel/stranded	09 45 751 1527	5 m
AWG 27/7 flexibel/stranded	09 45 751 1525	3 m
AWG 27/7 flexibel/stranded	09 45 751 1523	1,5 m
massiv / flexibel solid / stranded	Bestell-Nr. Part-No.	Maß a Dim. a



All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
				Dat.	Name	Maßstab/Scale 2:1	RJ45 Kabel 8xAWG 27 IP20 RJ45 Cable 8xAWG 27 IP20 2x RJ45 Plastic
			Detail.	21.06.04	Wie		
			Insp.	21.06.04	Wae		
32192	16.08.04	Wie	Stand.				
32089	20.07.04	Wie					
32073							
Mod.	Dat.	Name	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				TB 09 45 751 1551
							81a11/ page