

Brady B-324 BRADYGLO (TM) SELF-STICKING POLYESTER

TDS No. B-324

Effective Date: 11/05/2015

Description:

Brady B-324 BradyGlo™ material is a glow-in-the-dark (photoluminescent) pressure sensitive polyester.

Details:

Use:

Brady B-324 is used for exit and directional signs, identification of fire alarms and extinguishers, low location egress pathway markings, and directional systems for escape or evacuations routes. In accordance with ASTM 2030-99: Recommended Uses of Photoluminescent Safety Markings.

Relevant Standards:

Meets or exceeds the following standards. ASTM E-2072-00 / ASTM E-2073-00, ASTM E-162, ASTM E-648, ASTM E-662, IMO Resolution A.752(18), ISO/CD 15370, Marine Safety Committee MSC.27(61), DIN 67 510 (Parts 1 - 4), and PSPA Standard 002 Part 2.

Meets OSHA 1910.37, Lloyd's Register SAS F050294.p.

Inherent Properties:

Brady B-324 is a non-toxic, non-radioactive, explosion safe (does not generate energy to induce explosions) material allowing for sanitary disposal.

Illuminescent Characteristics:

Charge time of 5 minutes @ 1000 Lux will charge the sign for +10 hours of glow time. Consistent glow life and unlimited rechargability throughout service life.

Illumination: 21.6 lux (2 foot-candles) for 2 hours with a 4100K cool white fluorescent lamp.

Luminance (after illumination):

10 minutes >25 mcd/m²

60 minutes >5 mcd/m²

90 minutes >3 mcd/m²

Adhesive Type:

Pressure Sensitive Acrylic

Substrate Type:

Phosphorescent Polyester Film

Standard Legend Colors:

Black, green, red, and blue

Thickness (PSTC-133):

0.008 in. (0.20 mm)

Adhesive Properties:

Adhesion to Stainless Steel (PSTC-101)

15 Minute Dwell (Avg.) - 110 oz/in

Ultimate Dwell (72hrs) (Avg.) - 110 oz/in

Abrasion Resistance (ASTM D4060-14 Standard Test Method for Abrasion Resistance of Organic Coatings by the Taber Abraser):

CS-10 Wheels, 250g wts.

Legend withstands up to 100 cycles

CS-17 Wheels, 1000g wts.

Substrate withstands up to 9000 cycles

Gloss (ASTM D-523):

60° - 121 Gloss Units

Minimum Application Temperature:

50°F (10°C)

Service Temperature:

-40°F to 176°F (-40°C to 80°C)

Expected Service Life of Adhesive and Printed Legend

Average of 5 years

Outdoor Applications:

Not recommended for outdoor application.

Chemical Resistance:

REAGENT	7 DAY IMMERSION	DIP TEST	RUB TEST
30% Sulfuric Acid	NE	NE	NE
10% Sulfuric Acid	NE	NE	NE
30% HCl	NE	NE	NE
10% HCl	NE	NE	NE
50% NaOH	F	NE	NE
10% NaOH	F	NE	NE
MEK	F	F	F
Acetone	F	F	F
5% Sodium Hypochlorite (bleach)	NE	NE	NE
10% Ammonia	NE	NE	NE
Methanol	F	F	F
IPA (Isopropanol)	F	F	F
ASTM #3 Oil	NE	NE	NE
SAE 20 Oil	NE	NE	NE
Alconox®	NE	NE	NE
Toluene	F	NE	F
Mineral Spirits	NE	NE	NE
Glacial Acetic Acid	F	F	F
5% Acetic Acid	NE	NE	NE
Diesel Fuel	NE	NE	NE
Heptane	NE	NE	NE
10% NaCl	NE	NE	NE
Turpentine	NE	NE	NE
Kerosene	F	NE	NE
DI Water	NE	NE	NE
Gasoline	F	NE	F

NE = No Effect

F = Failed (affected sample)

7 Day Immersion: Immersed in reagent for 7 days.

Dip Test: Five 10 minute dips in reagent with 30 minute recovery.

Rub Test: Rubbed sample for 1 minute with swab soaked in reagent.

Product testing, customer feedback, and history of similar products, support a customer performance expectation of at least **two years from the date of receipt** for this product as long as this product is stored in its original packaging in an environment *below 80°F (27°C) and 60% RH*. We are confident that our product will perform well beyond this time frame. However, it remains the responsibility of the user to assess the risk of using such product. We encourage customers to develop functional testing protocols that will qualify a product's fitness for use in their actual applications.

Trademarks:

ANSI: American National Standards Institute (U.S.A.)

ASTM: American Society for Testing and Materials (U.S.A.)

Alconox® is a registered trademark of Alconox Co.

BradyGlo™ is a trademark of Brady Worldwide, Inc.

DIN: Deutsches Institut für Normung
Fed. Spec.: United States Federal Specification (U.S.A.)
IMO: International Maritime Association
OSHA: Occupational Safety & Health Administration
PSPA: Photoluminescent Safety Products Association
PSTC: Pressure Sensitive Tape Council (U.S.A.)

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2016 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289