

Description

type (TYP)	6213 - 6213
Generation (GEN)	00 - NO DESCRIPTION
circuit function (WW)	A - 2/2-WAYS; NORMALLY CLOSED
orifice size (DN)	13,0 - 13MM (1/2")
seal material (DWST)	BB - NBR
body material (WKST)	MS - BRASS
port connection (LTA)	GM84 - G1/2 THREADED PORT
coil size (SG)	7 - 43 MM
Voltage (SP)	024 - 24 VOLTS
frequency (FR)	UC - AC/DC
power consumption (LEIS)	CE - 60 WATT INRUSH, 3 WATT HOLD D
Variable Code 1 (VAR1)	JF94 - CONNECTOR 2511 WITH HL-EL ECTRONIC
Variable Code 2 (VAR2)	KM86 - LABEL COMPANY SIGN RS COM PONENTS
GMBH	
AND CIENT ORDER-NUMBER	
Identnumber	00150385
Key	6213-00-A13,0BBMSGM84-7-024/UC-CE * JF94+KM86
BSTALT	
Substitute-ID	
ConformitySign	CE01
Description	2/2-WAY SOLENOID VALVE, DIAPHR.-CPLD

Technical Data

PRESS. MAX. (BAR) (DRMAXBAR)	10
PRESS MAX. (PSI) (DRMAXPSI)	145
PRESS. MIN. (BAR) (DRMINBAR)	0
PRESS. MIN (PSI) (DRMINPSI)	0
REQUIRED PILOT PRESS.F.MAX.FLUID PRESS.(BAR) (STDRERFBAR)	
REQUIRED PILOT PRESS.F.MAX.FLUID PRESS.(PSI) (STDRERFPSI)	
PILOT PRESS. MAX (BAR) (STDRMAXBAR)	
PILOT PRESS MAX. (PSI) (STDRMAXPSI)	
PILOT PRESS. MIN. (BAR) (STDRMINBAR)	
PILOT PRESS. MIN. (PSI) (STDRMINPSI)	
KV-VALUE (M ³ /H) (KV)	3.600
QNN-VALUE (L/MIN) (QNN)	0
WEIGHT (KG) (MASSE)	0.725
FLUID TEMP. MAX. (DEGREE C) (MEDTEMPMAX)	+90
FLUID TEMP. MIN. (DEGREE C) (MEDTEMPMIN)	-10
AMB. TEMP. MAX. (DEGREE C) (UMGTEMPMAX)	+55
AMB. TEMP. MIN. (DEGREE C) (UMGTEMPMIN)	
PRESSURE (DRUCK)	
SWITCH-ON TIME(%) (ESDAUER)	100
OPENING TIME MAX. (MS) (TOEFFMAX)	100
OPENING TIME MIN. (MS) (TOEFFMIN)	50
CYCLING RATE (1/MIN) (SH)	20
CLOSING TIME MAX. (MS) (TSCHLMAX)	400
CLOSING TIME MIN. (MS) (TSCHLMIN)	200