




FEATURES:

- Accepts standard banana plugs
- Mounts in panels from 1.57 (.062) to 6.35 (.250) thick.

MATERIALS:

Insulated Captive Thumb Nut: Brass

Finish: Nickel plated brass

Insulation: Polycarbonate

Mounting Base: Polycarbonate

Insulator: Polycarbonate

Lockwasher: Steel

Hex Nut: Brass

Binding Post: Nickel plated brass;

Terminal: Gold Plated phosphor bronze

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 2500 WVDC Max.

Operating Temperature: +115°C (+239°F) Max.

Current: 3 Amperes

ORDERING INFORMATION: Model 4098-*

*=Color, -0 Black, -2 Red

Ordering Example: 4098-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA