

DO NOT SCALE PRINT

Honeywell

SWITCH - BASIC

CATALOGUE LISTING

V5C010BB1D

V5C010BB1D


REPLACES

M

DRAWING NUMBER

ISSUE

RELEASE NUMBER CN-13409




NOTES :-

1. MOUNTING HOLES WILL ACCEPT Ø3 MAX PINS OR SCREWS.
2. TERMINALS WILL ACCEPT 6.3 WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.

THIRD ANGLE PROJECTION



5.87			
RD			
CHECK			
DESIGN			
AUTHOR			

CHARACTERISTICS	
OPERATING FORCE	240g MAX
DIFFERENTIAL FORCE	
RELEASE FORCE	40g MIN
FREE POSITION	
PRETRAVEL	1.6 MAX
DIFFERENTIAL TRAVEL	0.25 MAX
OVERTRAVEL	0.8 MIN
FULL OVERTRAVEL FORCE	

ELECTRICAL DATA	
CONTACT ARRANGEMENT S.P.D.T.	
NL67	19
10(3)A 250V ~	
T85 µ 5E4	

SCALE :-	1/1
DIMENSIONS ARE IN MILLIMETRES	
TOLERANCES UNLESS OTHERWISE STATED	
±0.4	
ANGULAR ±	
MODIFY ON CAD3D SYSTEM ONLY	