





PANDUIT PART NO.	USE WITH THESE CABLE TIE CROSS-SECTIONS	DIMENSIONS				WEIGHT g/100pcs
		A	B	C	D	
PM2H25	MINIATURE INTERMEDIATE STANDARD	.62 (15.8)	.18 (4.6) REF	.30 (7.6)	.38 (9.6)	.10 (.45)

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, AND COLOR.
- (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- APPLICATION SPECIFICATION:
HOLE DIAMETER: .245 (6.3) - .255 (6.5)
PANEL THICKNESS: .125 (3.2) (MAX)



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G002391J_PB_PM2H25_03

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

PUSH MOUNT
PM2H25UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE
PROJECTION.

DRAWN BY

MAT'L:

SCALE

5:2

DATE

01-20-02

NYLON 6/6

DRAWING NO.

GB02391J

DWG

A

CHK'D

SIZE

3	5/27/08	DJSM		CORRECTED FILE NAME	GB02391J	3			
2	5/22/08	DJSM		TABULARIZED DIMENSIONS, REMOVED WINDOW DIMENSIONS	GB02391J	2			
1	02/05/03	MSAD		.070 +/- .015 WAS .070 +/- .010 (1.8 +/- 0.38) (1.8 +/- 0.25)	GB02391J	1			
R	01/10/02	LGG		INITIAL RELEASE	GB02391J	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	