




REV. 0
DCO 142815


COIL: @ 25°C
RESISTANCE 390 OHMS ±20%
NOMINAL VOLTAGE 12.0 VDC
MUST OPERATE 8.4 VDC
MUST RELEASE

ENVIRONMENT:

VIBRATION 10 CPS TO 500 CPS @ 10 g's
SHOCK 30 g's 6 MS. DURATION
TEMPERATURE -55 °C TO +85 °C

NOTES: OPERATE TIME 4 MS MAX
RELEASE TIME 3 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 3/14/01

CK. 3/14/01



COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD.
CUST. NO. REV.

MW4 RELAY
4 GHz

MW4-12A