



General ordering data

Order No.	1816790000
Part designation	VG M20-Exe/d MSN 3-8
Version	Cable gland, Brass, External thread: M 20 x 1.5
EAN	4032248308774
Qty.	5 pc(s).

General details

AF size 1	24 mm
Assembly temperature, max.	100 °C
Assembly temperature, min.	-60 °C
Clamping range, max.	8 mm
Clamping range, min.	3 mm
External thread	M 20 x 1.5
Length	53 mm
Length of thread	15 mm
Material	Brass
Protection class	IP 68
Sealing	Neoprene
Type of cable gland	metric

Approvals

Approvals institutes	n.a.
----------------------	------

Classifications

ETIM 2.0	EC000441
ETIM 3.0	EC000441
eClass 4.1	27-14-12-11
eClass 5.0	27-14-91-11
eClass 5.1	27-14-91-11

Similar products

Order No.	Part designation	Version
1816720000	VG M20-Exe/d MSN 11-	Cable gland, Brass, External thread: M 20 x 1.5
1816710000	VG M20-Exe/d MSN 7,5-	Cable gland, Brass, External thread: M 20 x 1.5
1816730000	VG M25-Exe/d MSN	Cable gland, Brass, External thread: M 25 x 1.5