

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

HSTT 12 - 48 0 2

COLOR

BLANK = BLACK 5 = GREEN  
1 = BROWN 6 = BLUE  
2 = RED 10 = WHITE  
3 = ORANGE 45 = YELLOW/GREEN  
4 = YELLOW C = CLEAR

QUANTITY PER CARTON (48 IN ONLY)

0 = 25pcs.  
5 = 5pcs.  
2 = 2pcs.

LENGTH IN"

INCHES

.5  
1  
48

FEET:


M=1000  
D=500  
T=200  
C=100  
L=50  
Q=25

TUBING SIZE - EXPANDED I.D.

TT = THIN WALL

TTV = THIN WALL VW-1 RATED

ID Ø



| PANDUIT<br>PART<br>NUMBER | Min.<br>Exp. I.D<br>In. (mm) | Max.<br>Rec. I.D<br>In. (mm) | RECOVERED<br>WALL<br>In. (mm) |
|---------------------------|------------------------------|------------------------------|-------------------------------|
| HSTT05                    | .046<br>(1.2)                | .023<br>(.6)                 | .016±.003<br>(.406±.076)      |
| HSTT06                    | .063<br>(1.6)                | .031<br>(.8)                 | .017±.003<br>(.432±.076)      |
| HSTT09                    | .093<br>(2.4)                | .046<br>(1.2)                | .020±.003<br>(.508±.076)      |
| HSTT12                    | .125<br>(3.2)                | .062<br>(1.6)                | .020±.003<br>(.508±.076)      |
| HSTT19                    | .187<br>(4.8)                | .093<br>(2.4)                | .020±.003<br>(.508±.076)      |
| HSTT25                    | .250<br>(6.4)                | .125<br>(3.2)                | .025±.003<br>(.635±.076)      |
| HSTT38                    | .375<br>(9.5)                | .187<br>(4.8)                | .025±.003<br>(.635±.076)      |
| HSTT50                    | .500<br>(12.7)               | .250<br>(6.4)                | .025±.003<br>(.635±.076)      |
| HSTT75                    | .750<br>(19.1)               | .375<br>(9.5)                | .030±.003<br>(.762±.076)      |
| HSTT100                   | 1.000<br>(25.4)              | .500<br>(12.7)               | .035±.005<br>(.889±.127)      |
| HSTT150                   | 1.500<br>(38.1)              | .750<br>(19.1)               | .040±.006<br>(1.016±.152)     |
| HSTT200                   | 2.000<br>(50.8)              | 1.000<br>(25.4)              | .045±.007<br>(1.143±.178)     |
| HSTT300                   | 3.000<br>(76.2)              | 1.500<br>(38.1)              | .050±.008<br>(1.270±.203)     |
| HSTT400                   | 4.000<br>(101.6)             | 2.000<br>(50.8)              | .055±.009<br>(1.397±.229)     |

#### NOTES:

- SHRINK RATIO: 2:1
- MATERIAL: CROSSLINKED POLYOLEFIN
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS

G03597HN\_DC\_G00239KH\_PB\_HSTT\_02

**PANDUIT**

CORP. TINLEY PARK, ILLINOIS

HSTT THIN WALL HEAT  
SHRINKABLE TUBING  
CUSTOMER DRAWING



UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) .XXX  
(.XX) .XXX

ANGLES ---

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN

IN INCHES, THIRD ANGLE PROJECTION.



|     |         |     |     |             |                                                                              |          |     |      |      |     |                      |           |                         |                  |
|-----|---------|-----|-----|-------------|------------------------------------------------------------------------------|----------|-----|------|------|-----|----------------------|-----------|-------------------------|------------------|
| 2   | 2/21/12 | LEF |     | △<br>△      | ADDED "CUSTOMER DRAWING" TO TITLE BLK<br>REMOVED ALL TOLERANCES IN TITLE BLK | GB0239KH | 2   | RAMI |      |     | DRAWN BY<br>LGRAVITT | MAT'L:    | SCALE<br>NONE           |                  |
| 1   | 10/5/11 | LEF |     | △<br>△      | ADD COLORS 1 & 3<br>CHANGE METRIC (19.0 TO 19.1)                             | GB0239KH | 1   | RAMI |      |     | DATE<br>5/12/03      | SEE NOTES | DRAWING NO.<br>GB0239KH | DWG<br>A<br>SIZE |
| REV | DATE    | BY  | CHK | DESCRIPTION |                                                                              |          | ECN | R    | CUST | SUP | CHK'D                |           |                         |                  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[HSTT75-48-5C](#)