

Search within category

GO

BUY NOW

DESIGN / INSTALL



UTPCH5MY

Category 5e, UTP patch cord with Pan-Plug™ Modular Plugs on each end. Off White, 5 meters.
UTPCH5MY replaces UTPCH5M

Specs

Packaging Details

Documents

★ Add to Favorites

Add to BOM

Conductor Gauge (AWG)	24
Performance Level	Category 5e
Note	UTPCH5MY replaces UTPCH5M
Overall Length (ft.)	16.41
Overall Length (m)	5
Maximum Operating Temperature (°C)	60
Maximum Operating Temperature (°F)	140
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Flammability Rating	CM
Standards Met	ANSI/TIA-568-C.2, ISO 11801 Class EA, IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
Cable Type	U/UTP
Cable Color	Off-White
Length (ft.)	16.41
Termination End 1	Modular Plug
Termination End 2	Modular Plug
CE Compliant	Yes
Nominal Cable Outside Diameter (In.)	0.22
Nominal Cable Outside Diameter (mm)	5.5
UL5A Listed	No
Boot Color	No Boot
Conductor Material	Copper
Maximum Installation Temperature (°C)	70

Maximum Installation Temperature (°F)	158
Minimum Installation Temperature (°C)	-40
Minimum Installation Temperature (°F)	-40
Part Features	100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch
RoHS Compliancy Status	Compliant
Min. Order Qty.	1