

Cord Connectors

Straight Male

Form Size 2-4

UL Listed to Type 4, 4X, 12 and Type 13


IP66*
 SUITABILITY

N.P.T. Hub Size	Cord Dia. Inches (mm)	Form Size	Color Code	Machined Aluminum	Machined Zinc-Plated Steel	Stainless Steel	Nylon Gray	Black
3/4"	.06"- .13" (1.6-3.2)		Green	SHC1029	•	•	•	•
	.13"- .19" (3.2-4.7)		Orange	SHC1030	SHC1030ZP	•	•	•
	.19"- .25" (4.7-6.3)	F2	Red	SHC1031	SHC1031ZP	•	•	•
	.25"- .38" (6.3-9.7)		White	SHC1032	SHC1032ZP	•	•	•
	.38"- .50" (9.7-12.7)		Blue	SHC1033	SHC1033ZP	•	•	•
	.50"- .63" (12.7-15.9)		Brown	SHC1034	SHC1034ZP	•	•	•
3/4"	.38"- .50" (9.5-12.7)		Blue	•	SHC1035ZP	SHC1035SS	SHC1035CR	SHC2035CR
	.50"- .63" (12.7-15.9)	F3	Brown	SHC1036	SHC1036ZP	SHC1036SS	SHC1036CR	SHC2036CR
	.63"- .75" (15.9-19.0)		Yellow	SHC1037	SHC1037ZP	SHC1037SS	SHC1037CR	SHC2037CR
	.75"- .88" (19.0-22.2)		Orchid	SHC1038**	SHC1038ZP**	SHC1038SS**	SHC1038CR**	SHC2038CR**
1"	.50"- .63" (12.7-15.9)	F3	Brown	•	SHC1097ZP	•	•	•
	.63"- .75" (15.9-19.0)		Yellow	•	SHC1098ZP	•	•	•
	.75"- .88" (19.0-22.2)		Orchid	•	SHC1099ZP	•	•	•
1"	.38"- .50" (9.7-12.7)		Blue	SHC1039	•	•	SHC1039CR	•
	.50"- .63" (12.7-15.9)		Brown	SHC1040	•	•	SHC1040CR	•
	.63"- .75" (15.9-19.0)	F4	Yellow	SHC1041	•	SHC1041SS	SHC1041CR	SHC2041CR
	.75"- .88" (19.0-22.2)		Orchid	SHC1042	•	SHC1042SS	SHC1042CR	SHC2042CR
	.88"- 1.00" (22.2-25.4)		Gray	SHC1043	SHC1043ZP	•	SHC1043CR	SHC2043CR
	1.00"- 1.13" (25.4-28.6)		Pink	SHC1044**	•	SHC1044SS**	SHC1044CR**	SHC2044CR**



Stainless Steel



Gray Nylon



Black Nylon

Note: See pages T-87 to T-98 for additional technical data and dimensional drawings.

*IP66 Suitability when used with optional metal clad O-ring shown on page T-83.

**Cable jacket may have to be stripped to pass through connector body.

Form 4 aluminum and plated steel nuts are machined, bodies are cast aluminum.