

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.


ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		EH02-0004-02	29 JAN 02	RC	RM
O		EH-0558-97	30 MAY 97	AM	DS



NOTES:

1. INSERTION LOSS $\leq 0,5$ dB, MEASURED AGAINST REF. CONNECTOR.2. RETURN LOSS ≥ 65 dB, MATED

△ APC ANGLE = 8°

4. CABLE:

- 9/125 μm
- DIAMETER: 3,0 mm
- COLOUR: YELLOW
- TIGHT BUFFER
- OUTER SHEATH MATERIAL: PVC

△ INFO ON CABLE LABEL:

- TYCO PART NUMBER
- P.O. NUMBER AND PROD. DATE (FORMAT YYWW)

EXAMPLE:

TYCO 0-0233888-2
0-1234-5 0204STANDARD LENGTHS ACCORDING TO
CUSTOMER DRAWING 1206850

PART NUMBER	"L" (METER) △
X-0233888-Y	XY,0

L	Part Number	Description	Item
2		CABLE $\varnothing 3,0$ mm	10
2		CABLE LABEL	9
2		CAP, PROTECTIVE, BLACK	8
2		BOOT, GREEN	7
2		CRIMP EYELET OPTIMATE 3,0mm	6
2		INTERNAL BODY, 3,0 mm	5
2		SPRING COMPRESSION 3,0 mm	4
2		FERR. SUBASSY	3
2		PLUG BODY, PRECISION KEYING	2
2		COUPLING NUT	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
MM	
0 PLC	$\pm$ -
1 PLC	$\pm$ -
2 PLC	$\pm$ -
3 PLC	$\pm$ -
4 PLC	$\pm$ -
ANGLES	$\pm$ -
FINISH	-

DWN	29 JAN 02
CHK	29 JAN 02
APVD	29 JAN 02
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

R.COOLEN		29 JAN 02		Tyco Electronics Corporation	
R.MAARTENS		29 JAN 02		's-Hertogenbosch Nederland	
R.MAARTENS		29 JAN 02		NAME	
PRODUCT SPEC		NAME		FOSM LEAD 3,0	
APPLICATION SPEC		NAME		FC/APC - FC/APC	
WEIGHT		NAME		RESTRICTED TO	
CUSTOMER DRAWING		NAME		RESTRICTED TO	
SCALE		SHEET		REV	
A2 00779		C=233888		A	