




NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-1 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128624C ASSEMBLY CONSISTS OF 128514C COLLET AND 128488 DRAWBAR.
- 5 128336-06C ASSEMBLY CONSISTS OF 127078C ANVIL HOLDER AND 127207-06 ANVIL INSERT

REV	DESCRIPTION	DET	DATE
C	REWROTE NOTES; ADDED .453 CENTER TO EDGE DIMENSION		11/24/09
D	128514C WAS 128624C. ADDED 128488	JJC	08/03/12

D	128488	1	DRAWBAR	9
	126748-1	1	UNITIZED DEFLECTOR	8
D	128514C	1	COLLET	7
	126745	1	GUARD	6
	120095	1	DEFLECTOR	5
	122912	1	BARBED RETAINER	4
	128078	1	UNITIZED CHUCK JAW	3
	127582	1	TOP GUARD	2
	128336-06C	1	ANVIL ASSEMBLY	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH			
ITAR:		HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DR, P.O. BOX 2270 KINGSTON, NEW YORK 12401	
ECCN: EAR99		NOSE ASSEMBLY -06 UAB BR LONG	
SCH B#: 8467.99.0190		DET: MJK	DATE: 11/15/06
HTS: 8467.99.0190		CK:	SCALE: 2:1
		B	99-3765-1C