

Bridge Rectifiers

[illegible]

WO 005M	50	35	1.5+	25	50	10	1.1	1.0	4-8
WO 01M	100	70	1.5+	25	50	10	1.1	1.0	
WO 02M	200	140	1.5+	25	50	10	1.1	1.0	
WO 04M	400	280	1.5+	25	50	10	1.1	1.0	
WO 06M	600	420	1.5+	25	50	10	1.1	1.0	
WO 08M	800	560	1.5+	25	50	10	1.1	1.0	
WO 10M	1000	700	1.5+	25	50	10	1.1	1.0	
2WO 005	50	35	2.0	25	50	10	1.1	1.0	4-8
2WO 01	100	70	2.0	25	50	10	1.1	1.0	
2WO 02	200	140	2.0	25	50	10	1.1	1.0	
2WO 04	400	280	2.0	25	50	10	1.1	1.0	
2WO 06	600	420	2.0	25	50	10	1.1	1.0	
2WO 08	800	560	2.0	25	50	10	1.1	1.0	
2WO 10	1000	700	2.0	25	50	10	1.1	1.0	
2WO 005M	50	35	2.0	25°	50	10	1.1	1.0	4-9
2WO 01M	100	70	2.0	25°	50	10	1.1	1.0	
2WO 02M	200	140	2.0	25°	50	10	1.1	1.0	
2WO 04M	400	280	2.0	25°	50	10	1.1	1.0	
2WO 06M	600	420	2.0	25°	50	10	1.1	1.0	
2WO 08M	800	560	2.0	25°	50	10	1.1	1.0	
2WO 10M	1000	700	2.0	25°	50	10	1.1	1.0	
S005	50	35	2.0+	35°	50	10	1.1	1.0	4-10
S001	100	70	2.0+	35°	50	10	1.1	1.0	
S002	200	140	2.0+	35°	50	10	1.1	1.0	
S004	400	280	2.0+	35°	50	10	1.1	1.0	
S006	600	420	2.0+	35°	50	10	1.1	1.0	
S08	800	560	2.0+	35°	50	10	1.1	1.0	
S10	1000	700	2.0+	35°	50	10	1.1	1.0	
KBPC1005	50	35	3.0+	50°	50	10	1.2	1.5	4-11
KBPC101	100	70	3.0+	50°	50	10	1.2	1.5	
KBPC102	200	140	3.0+	50°	50	10	1.2	1.5	
KBPC104	400	280	3.0+	50°	50	10	1.2	1.5	
KBPC106	600	420	3.0+	50°	50	10	1.2	1.5	
KBPC108	800	560	3.0+	50°	50	10	1.2	1.5	
KBPC110	1000	700	3.0+	50°	50	10	1.2	1.5	
PW005	50	35	6.0+	45°	200	10	1.3	3.0	4-12
PW01	100	70	6.0+	45°	200	10	1.3	3.0	
PW02	200	140	6.0+	45°	200	10	1.3	3.0	
PW04	400	280	6.0+	45°	200	10	1.3	3.0	
PW06	600	420	6.0+	45°	200	10	1.3	3.0	

PW08	800	560	6.0+	45°	200	10	1.3	3.0	
KBPC8005	50	35	8.0	50°	125	10	1.2	3.0	4-13
KBPC801	100	70	8.0	50°	125	10	1.2	3.0	
KBPC802	200	140	8.0	50°	125	10	1.2	3.0	
KBPC804	400	280	8.0	50°	125	10	1.2	3.0	
KBPC806	600	420	8.0	50°	125	10	1.2	3.0	
KBPC808	800	560	8.0	50°	125	10	1.2	3.0	
KBPC810	1000	700	8.0	50°	125	10	1.2	3.0	
J005	50	35	10+	45°	200	10	1.1	5.0	4-14
J01	100	70	10+	45°	200	10	1.1	5.0	
J02	200	140	10+	45°	200	10	1.1	5.0	
J04	400	280	10+	45°	200	10	1.1	5.0	
J06	600	420	10+	45°	200	10	1.1	5.0	
KBPC10005	50	35	10+	55°	200	10	1.2	5.0	4-15
KBPC1001	100	70	10+	55°	200	10	1.2	5.0	
KBPC1002	200	140	10+	55°	200	10	1.2	5.0	
KBPC1004	400	280	10+	55°	200	10	1.2	5.0	
KBPC1006	600	420	10+	55°	200	10	1.2	5.0	
KBPC1008	800	560	10+	55°	200	10	1.2	5.0	
KBPC1010	1000	700	10+	55°	200	10	1.2	5.0	
K005	50	35	25+	45°	300	10	1.2	12.5	4-14
K01	100	70	25+	45°	300	10	1.2	12.5	
K02	200	140	25+	45°	300	10	1.2	12.5	
K04	400	280	25+	45°	300	10	1.2	12.5	
K06	600	420	25+	45°	300	10	1.2	12.5	
KBPC25005	50	35	25+	55°	300	10	1.2	12.5	4-15
KBPC2501	100	70	25+	55°	300	10	1.2	12.5	
KBPC2502	200	140	25+	55°	300	10	1.2	12.5	
KBPC2504	400	280	25+	55°	300	10	1.2	12.5	
KBPC2506	600	420	25+	55°	300	10	1.2	12.5	
KBPC2508	800	560	25+	55°	300	10	1.2	12.5	
KBPC2510	1000	700	25+	55°	300	10	1.2	12.5	
KBPC35005	50	35	35	55	300	10	1.2	17.5	4-15
KBPC3501	100	70	35	55	300	10	1.2	17.5	
KBPC3502	200	140	35	55	300	10	1.2	17.5	
KBPC3504	400	280	35	55	300	10	1.2	17.5	
KBPC3506	600	420	35	55	300	10	1.2	17.5	
KBPC3508	800	560	35	55	300	10	1.2	17.5	
KBPC3510	1000	700	35	55	300	10	1.2	17.5	

* For capacitive load + For R and L load

****.The Mechanical Outline & circuit diagram can be download on the same directory.***