





809 950
809 962



Connectors



Type	VON 10	VON 20	VON 30
Order no.	930 045- . . . (see colour index below)*	930 046- . . . (see colour index below)*	930 047- . . . (see colour index below)*
Quantity boxed	100 each	100 each	100 each
Dimensions			



Description	Fully mating connector, polystyrene insulating sleeve, screwed on. Screw connection up to a maximum conductor cross-section of 1.5 mm ² Nickel-plated brass contact	Fully mating connector, shatter-proof flexible insulating sleeve. The sleeve narrows at the end to prevent the cable from buckling Screw connection up to a maximum conductor cross-section of 1.5 mm ² . Nickel-plated brass contact	Fully mating connector, shatter-proof flexible insulating sleeve. The sleeve narrows at the end to protect the cable against buckling Solder connection up to a maximum conductor cross-section of 1.5 mm ² Nickel-plated brass contact
-------------	--	--	--

Technical data

Type of connection	screw	screw	solder
Continuous load current	16 A	16 A	16 A
Volume resistance (max.)	3 mΩ	3 mΩ	3 mΩ
Permissible temperature range	-25 °C . . . +70 °C	-25 °C . . . +70 °C	-25 °C . . . +70 °C
Colour index*	black	-100	-100
	red	-101	-101
	blue	-102	-102
	yellow	-103	-103
	green	-104	-104
	assorted cirs.	930 271-000 (VON 10 F)	

Version VON 10 F in assorted colours is made up of 20 connectors in each of the colours black, red, blue, yellow and green

4 mm dia.
laboratory equipment