



5 Pin DIN Plugs

17DN100, 17DN101

KOBI CONN

5 Pin DIN Plugs

17DN100, 17DN101



Dimensions: In.

SPECIFICATIONS

Withstand Voltage:	500V @ 1min
Insulation Resistance:	100MΩ
Contact Resistance:	30mΩ
Solder Cup:	Accepts 24-AWG wire
Cable Strain Relief:	6-8mm OD

MouserStock No.	No. of Pins	Color	Degrees of ARC
17DN100	5	Gray	180
17DN101	5	Black	180

Date Last Revised: 6/21/12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300041

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[17DN101](#) [17DN100](#)