



Re-sealable protective sleeving for post-termination cable organisation

• HELAHOOK

Features and Benefits

HELAHOOK is a lightweight, abrasion resistant and re-sealable protective sleeving. Due to its hook-and-loop sealing system, HELAHOOK can be used to protect cables and hoses that are already fixed. It adapts to very irregular shapes and sizes. It permits quick and easy access to enclosed components and can be used repeatedly. It is therefore a sensible alternative to braided sleeving and corrugated tubing for many common applications.

HELAHOOK has good fire-protection properties. It complies with the standard NF F 16-101, Class F1 for smoke emission and gas toxicity and meets UL94 V2.

Application

HELAHOOK is used in industrial machines, electrical appliances, shipbuilding, railway vehicles and in the aerospace industry. HELAHOOK is also employed in automobiles or commercial vehicles. It is the ideal solution for post-termination cable organisation and wherever repeated use is a necessity.



HELAHOOK protective sleeving allows for retrospective fitting and repeated use.



HELAHOOK provides excellent abrasion resistance.

Material Data

Material	Polyester (PET)
Colour	Black (BK)
Operating Temperature	-50 °C to +150 °C
Flammability	UL94 V2, FMVSS 302
Specification	NF F 16-101



Technical Table

Article-No.	Type	Bundle Ø min.	Bundle Ø max.	Reel Length (m)
170-05100	HELAHOOK10	3	15	25
170-05150	HELAHOOK15	10	20	25
170-05200	HELAHOOK20	15	30	25
170-05250	HELAHOOK25	20	40	25
170-05300	HELAHOOK30	25	50	25

All dimensions in mm. Subject to technical changes.

Cuts in any lengths are available on request.