

Wiha Cabinet Tip Screwdrivers


[SHOP](#)

186 Slotted Cabinet Tip Screwdriver, With Wiha-Square Handle
Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated.
Tip parallel to shaft. Series includes extra long dimensions for screws in difficult to reach locations. Wiha-square handle cellulose-acetate, impact resistant.

Item	1	2	3	4	5	6	7	8	9	10
No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
186 01	2.0	.08	40	1.6	0.40	.02	100	4.0	.02	10
186 03	2.5	.10	50	2.0	0.40	.02	110	4.3	.02	10
186 06	3.0	.12	75	3.0	0.50	.02	150	5.9	.05	10
186 09	3.0	.12	100	3.9	0.50	.02	175	6.9	.06	10
186 12	3.0	.12	150	5.9	0.50	.02	225	8.9	.06	10
186 15	3.0	.12	200	8.0	0.50	.02	285	11.2	.08	10
186 24	4.0	.16	100	3.9	0.60	.02	185	7.3	.08	10
186 27	4.0	.16	150	5.9	0.60	.02	235	9.3	.10	10
186 30	4.0	.16	200	8.0	0.60	.02	285	11.2	.11	10
186 42	5.0	.20	100	3.9	0.70	.03	195	7.7	.13	10
186 45	5.0	.20	150	5.9	0.70	.03	245	9.6	.15	10
186 48	5.0	.20	200	8.0	0.70	.03	295	11.6	.17	10
186 51	5.0	.20	300	12.0	0.70	.03	395	15.6	.20	10
186 54	6.0	.24	100	3.9	0.90	.04	205	8.1	.19	10
186 57	6.0	.24	150	5.9	0.90	.04	255	10.0	.21	10
186 60	6.0	.24	200	8.0	0.90	.04	305	12.0	.24	10
186 63	6.0	.24	300	12.0	0.90	.04	405	15.9	.29	10
186 72	8.0	.32	200	8.0	1.20	.05	315	12.4	.32	10
186 78	8.0	.32	300	12.0	1.20	.05	415	16.3	.39	10
186 81	10.0	.39	200	8.0	1.60	.06	315	12.4	.37	10


[SHOP](#)

153 Phillips Screwdriver, With Wiha-Square Handle
Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated.
Wiha-square handle cellulose-acetate, impact resistant.

Item	1	2	3	4	5	6	7	8	9	10
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
153 05	0	60	2.4	3.0	.12	135	5.3	.05	10	
153 10	1	80	3.1	4.5	.18	175	6.9	.11	10	
153 15	1	200	8.0	4.5	.18	295	11.6	.15	10	
153 25	2	100	3.9	6.0	.24	205	8.1	.18	10	
153 30	2	250	10.0	6.0	.24	355	14.0	.27	10	
153 35	2	350	13.7	6.0	.24	455	17.8	.33	10	
153 40	3	150	5.9	8.0	.32	265	10.4	.33	10	


[SHOP](#)

222 Pozidriv® Screwdriver, With Wiha-Square Handle
Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated.
Wiha-square handle cellulose-acetate, impact resistant.

Item	1	2	3	4	5	6	7	8	9	10
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
222 20	1	200	8.0	4.5	.17	295	11.6	.15	10	
222 30	2	250	9.8	6.0	.23	355	13.9	.27	10	

Wiha Awls Screwdrivers


[SHOP](#)

300 02 Square Reaming Awl, With Plastic Handle
Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated.
Round handle cellulose-acetate, impact resistant.

Item	1	2	3	4	5	6	7	8	9	10
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.		
300 02	6.0	.236	100	3.9	185	7.3	.15	10		


[SHOP](#)

301 02 Round Awl, With Plastic Handle
Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated.
Plastic handle cellulose-acetate, impact resistant.

Item	1	2	3	4	5	6	7	8	9	10
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.		
301 02	6.0	.236	100	4.0	185	7.3	.15	10		

Wiha Offset Screwdrivers


[SHOP](#)

161 Phillips Offset Screwdriver, With Handle
For working in confined spaces. Blade CVM special steel, hardened, hard chromed. Handle high quality plastic, impact resistant.

Item	1	2	3	4	5	6	7	8	9	10
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.			
161 12	1 + 2	125	4.9	5.5	.217	.08	10			
161 34	3 + 4	200	8.0	10.0	.315	.33	10			

207 Slotted Offset Screwdriver, With Handle

Item	1	2	3	4	5	6	7	8	9	10
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.		
207 00	3.5	9/64	90	3.5	0.6	.02	.02	10		
207 05	4.0	5/32	100	3.9	0.8	.03	.03	.10		
207 10	5.5	7/32	125	5.0	1.0	.04	.06	10		
207 15	6.5	1/4	125	5.0	1.2	.05	.07	10		
207 20	8.0	5/16	150	5.9	1.2	.05	.15	10		
207 25	10.0	3/8	175	6.9	1.6	.06	.23	10		


[SHOP](#)

207 90 5 Pc. Set Slotted & Phillips Offset Screwdrivers

Item	1	2	3	4	5	6	7	8	9	10
No.	lbs.	Set includes the following drivers:								
207 90	.86	Slotted: 6.5, 8.0, 10.0								
		Phillips: 1 + 2, 3 + 4								