



Cubitron II Abrasives

[Products](#) | [Technology](#) | [Resources](#) | [Testimonials](#)

[United States](#) > [Products & Services](#) > [Manufacturing and Industry](#) > [Cubitron II](#) > [Products](#) > [Cable/Wire](#) > 3M™ Round, Shielded/Jacketed, Flat Cable, 3659 Series3659/64, 100 ft.

3M™ Round, Shielded/Jacketed, Flat Cable, 3659 Series3659/64, 100 ft.

UPC# 00051138420871 3M Product Number 3659/64 3M ID 80610802516

Print Share



.050" 28 AWG Stranded, Mass Terminatable, PVC/PVC, 100 ft.

- Round construction permits easier routing
- 28 AWG wire on .050 inch pitch permits mass termination to broad line of IDC connectors
- Continuous split/bond repeat allows for mass termination on 2.4 inch centers (approximate)
- Primary cable is zippable for branching or discrete terminations
- Meets external wiring requirements of National Electrical Code, Article 725 (CL2)
- UL listed for USA and Canadian markets
- Dual shielding provides 35 db average shielding effectiveness
- RoHS Compliant

www.facebook.com
is not loading.

Need Help?

Questions? We can help
[Contact Us](#)

[Overview](#) [Support](#)

Specifications

Color	Gray
Shape	Round

People who viewed this item also viewed



3M™ 4-Wall Header .100 in., High Temp Option, Straight, 30 Contacts, 3440-6302



3M™ Round Conductor Flat Cable, 3801 Series, C3801/14, 100 ft.



3M™ Round Conductor Flat Cable, 3365 Series, 3365/10, 100 ft.



3M™ Round Conductor Flat Cable, 3365 Series, 3365/25, 100 ft.



3M™ High Flex Life Cable, 3319 Series, 3319/14, 100 ft.