



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	TAB SIZE	WIRE RANGE AWG	COLOR	MAX. INSUL.	DIMENSIONS in.		
					A $\pm .03$	B $\pm .01$	C $\pm .01$
DV10-250	.250 X .032	12-10	YELLOW	.229 (5.82)	1.03 (26.16)	.30 (7.62)	.13 (3.30)

NOTES:

- UL RECOGNIZED AND CSA CERTIFIED FOR:
 - 600V MAX VOLTAGE RATING
 - 194°F (90°C) MAX TEMP RATING
 - STRANDED COPPER WIRE ONLY
 - 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
 - 24 AMP. MAX.
- MATERIAL:
 - STAMPING-BRASS, TIN PLATED
 - HOUSING-VINYL
 - SLEEVE-BRASS, TIN PLATED
- DIMENSIONS IN BRACKETS ARE IN mm OR mm²
- INSTALLATION TOOLS: UL/CSA: CT-550, CT-1551,
PANDUIT RECOMMENDED: CT-100
CT-160
CT-260
CT-460
- PACKAGE QTY: -L:50
-D:500
- WIRE STRIP LENGTH: 9/32 $\pm .001$ (7.1 $\pm .0$)



CERTIFIED
LR31212



RECOGNIZED
E78522

A41199_04

04	1/01	KMD		CAD FILE SPEC. WAS N41199AA_PCD_03				PANDUIT CORP. TINLEY PARK, ILLINOIS
03	5/99	JKD		ADDED CT-1551 & CT-1550 TOOLS	07642			
02	3/95	MS	RLS	UPDATED NOTES AND DIMENSIONS	03048	LA	JB	FEMALE DISCONNECTS, VINYL INSULATED .250 X .032
01	1/89	SM	DM	REVISED DET TO MATCH STAMPING		LA	JB	
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY FES Ck'D RLS SCALE NONE DRAWING NO. A41199