


2mm

LED CBI® Circuit Board Indicator (DIN 41494 Compatible), Tri-Level

Dialight

570-0100-xxx



PART NO.

COLOR*

570-0100-111
570-0100-132
570-0100-222
570-0100-333

Red-Red-Red
Red-Yellow-Green
Green-Green-Green
Yellow-Yellow-Yellow

* Top-Middle-Bottom LED

LED Data

- For absolute maximum ratings and other electrical/optical data, refer to LED data sheet.


3

Benefits

- DIN 41494 compatible
- 2mm Tri-Level for high density status indication
- Available with mixed colors
- Housing material UL94 V-0 rated
- Black housing enhances contrast
- Vibration and shock resistant
- Housing assures proper LED alignment
- Single PC board insertion - 3 LEDs

Custom Combinations

- Contact factory for information on custom color combinations.



CLICK HERE

To Construct Custom Color Combinations of This Part

Typical Operating Characteristics (TA=25°C)

Part Number	Color	Peak Wavelength nm	Iv* mcd	Vf** Volts	Viewing Angle 2θ½	LED Data sheet	Page #
570-0100-xxx	Red	635	12.6	2	38°	521-9630	3-13
	Green	565	8.7	2.1	38°	521-9632	3-13
	Yellow	585	12.6	2.1	38°	521-9631	3-13

* I_F = 10 mA **I_F = 20 mA