


15 mm carbon pre-set potentiometer series H/V A 15

- Closed version
- Both side setting, insulated slider
- Linear or logarithmic resistance law
- Resistance tolerance:
 - $\pm 20\%$ for value $R \leq 1\text{M}\Omega$
 - $\pm 30\%$ for value $R > 1\text{M}\Omega$
- On special request closer tolerances are available
- Mechanical endurance 10000 cycles




Rated dissipation at $\vartheta_{\text{amb}} = 40^\circ\text{C}$	lin 0.25W / log 0.12W
Resistance value range	lin 100 Ω to 5M Ω / log 2.2K Ω to 2.5M Ω
Maximum voltage	lin 300V dc / log 200V dc
Electric angle of rotation	$250^\circ \pm 20^\circ$
Mechanical angle of rotation	$265^\circ \pm 5^\circ$
Operating torque	4 to 25 mNm
End stop torque	$\geq 100\text{ mNm}$
Weight	1.3 g approx.


HA 15 / 30 (10x12,5)




HA 15 / 30 (10x15)




HA 15 / 30 (10x12,5) long terminals




VA 15 / 30 (5x5)



ADJUSTMENT SLOT




THUMBWHEEL



Thumbwheel Colour	Code
White	88 131 147
Black	88 131 388
Red	88 131 391
Blue	88 131 390
Green	88 131 392
Yellow	88 131 389

SHAFT



SHAFT COLLOR CODES

Colour \ L	13.1	17.5	19.5	24.3	26.3	28.5	34
White	88 131 137	88 131 577	88 131 242	88 131 600	88 131 499	88 131 578	88 131 450
Black	88 131 378	88 131 241	88 131 382	88 131 243	88 131 244	88 131 245	88 131 246
Red	88 131 379	88 131 452	88 131 385	88 131 492	88 131 475	88 131 770	88 131 491
Blue	88 131 381	88 131 752	88 131 386	88 131 581			
Green	88 131 380		88 131 384				
Yellow	88 131 620		88 131 619				

AB Elektronik Sachsen GmbH
Salzstrasse 3
01774 Klingenberg / Germany

www.abelektronik.com

