




Specification:

Materials:

Shell: Tin Plated Steel
Insulator: PBT Thermo Plastic, Black Color, 30% Glass Filled
Self-Extinguishing, UL94V-0 rated
Contact Material: Pin: Brass, Socket: Phosphor Bronze
Contact Plating: Gold over Nickel

Electrical:

Current Rating: 5.0 Amps
Dielectric Strength: 1000 VAC min.
Insulation Resistance: 5000m ohm min
Operating Temperature Range: -55°C~+125°C

Dimensions

# of Pins	A	B	C
9	16.33	24.99	30.81
	.643	.984	1.213
15	24.66	33.32	39.14
	.971	1.312	1.541
25	38.38	47.04	53.04
	1.511	1.852	2.088
37	54.84	63.50	69.32
	2.159	2.500	2.729

Features and Options:

- Available in 9, 15, 25, and 37 positions
- Male and Female Versions
- Available with hardware options such as threaded inserts and hex stands-offs, board locks and grounding straps
- Gold plated contacts
- Tin plated shell

Description	
Name :	
A-DXXXA-KG-TXXX3	
D-Sub Connector Right Angle	
ASSMANN Electronic Components	



THIS DRAWING IS UNPUBLISHED
© Copyright 2005 by Assmann Electronic Components All International Rights Reserved
This drawing is a controlled document for Assmann Electronics, Inc. It is subject to change and the controlling engineering organization should be contacted for the latest revision.