



STAR SEA

Product Search:

3721••••ç•μ•û£••••£μç×•

| About Us

| Products

| Contact Us

| Culture

| Web Manage

| Home |

中文版

Location: [Product Search](#)

3.0 AMPERES/SMC(DO-214AB)



TYPE	Maximum Peak Reverse Voltage PRV V_{PK}	Maximum Average Rectified Current @Half-wave Resistive Load 60Hz I_O @ T_A A_{AV}	Maximum Average Rectified Current @Half-wave Resistive Load 60Hz I_O @ T_A °C	Maximum Forward Peak Surge Current @8.3ms Superimposed I_{FM} (Surge) A_{PK}	Maximum Reverse Current @PRV @25°C T_A I_R μ •A _{dc}	Maximum Forward Voltage @25°C T_A I_{FM} A_{PK}	Maximum Forward Voltage @25°C T_A V_{FM} V_{PK}	
S3A	50	3.0	75	100	10	3.0	1.2	
S3B	100	3.0	75	100	10	3.0	1.2	
S3D	200	3.0	75	100	10	3.0	1.2	
S3G	400	3.0	75	100	10	3.0	1.2	
S3J	600	3.0	75	100	10	3.0	1.2	
S3K	800	3.0	75	100	10	3.0	1.2	
S3M	1000	3.0	75	100	10	3.0	1.2	

OPERATIONG AND STORAGE TEMPERATURE -65°C TO +175°C

Copyright 2003 Changzhou Star Sea Electronics Co.,Ltd. All right Reserved.

Add: 18 Sanjing Road West, Changzhou, Jiangsu, China

Tel: +86-519-5111018 5111098 Fax: +86-519-5112846 5122846

E-mail: starsea@public.cz.js.cn P.C.: 213022